

Report of Test

LLIA001589-001


Indoor Distribution Photometry Test Report

Catalog Number: LHB80W-850-EX39

Pendent mounted high bay replacement lamp, E39 screw base, plastic housing, aluminum heat sink, clear plastic enclosure with concentric lenses below LEDs.

264 white LEDs.

Integral LED driver



Prepared For:

Topaz Lighting Corp

925 Waverly Avenue

Holtsville, NY 11742, USA

Performance Summary


Input Voltage	120.0 Vac	Luminous Flux	11208.0 Lumens
Input Current	0.6475 A	Total Efficacy	146.0 Lm/W
Input Power	76.76 W	Downward Flux	11106.4 Lumens
Frequency	60.00 Hz	Downward Flux	99.1 % of Total
Power Factor	0.988		
Current THD	9.6 %		

This test report was issued by LightLab International Allentown, LLC without alterations or erasures.


Test date: 11/18/2021

Report date: 11/19/2021


Signed: _____



Report of Test
LLIA001589-001



Zonal Flux Summary										
Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total		Zone (Deg Vert)	Flux (Lumens)	Percent of Total
0-10	370.7	3.3%		90-100	24.0	0.2%		0-20	1488	13.3%
10-20	1117	10.0%		100-110	16.7	0.1%		0-30	3272	29.2%
20-30	1784	15.9%		110-120	13.6	0.1%		0-40	5311	47.4%
30-40	2039	18.2%		120-130	12.7	0.1%		0-60	9017	80.5%
40-50	1926	17.2%		130-140	12.3	0.1%		0-80	11000	98.1%
50-60	1780	15.9%		140-150	10.3	0.1%		10-90	10736	95.8%
60-70	1343	12.0%		150-160	7.3	0.1%		20-50	5749	51.3%
70-80	639.6	5.7%		160-170	3.9	0.0%		40-90	5795	51.7%
80-90	106.7	1.0%		170-180	0.9	0.0%		60-90	2089	18.6%
0-90	11106	99.1%		90-180	101.6	0.9%		0-180	11208	100.0%




Report of Test

LLIA001589-001

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles								
		0	22.5	45	67.5	90	112.5	135	157.5	180
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	0	3865	3865	3865	3865	3865	3865	3865	3865	3865
	2.5	3868	3868	3868	3868	3868	3868	3868	3868	3868
	5	3876	3876	3876	3876	3876	3876	3876	3876	3876
	7.5	3883	3883	3883	3883	3883	3883	3883	3883	3883
	10	3893	3893	3893	3893	3893	3893	3893	3893	3893
	12.5	3914	3914	3914	3914	3914	3914	3914	3914	3914
	15	3943	3943	3943	3943	3943	3943	3943	3943	3943
	17.5	3964	3964	3964	3964	3964	3964	3964	3964	3964
	20	3958	3958	3958	3958	3958	3958	3958	3958	3958
	22.5	3922	3922	3922	3922	3922	3922	3922	3922	3922
	25	3875	3875	3875	3875	3875	3875	3875	3875	3875
	27.5	3815	3815	3815	3815	3815	3815	3815	3815	3815
	30	3694	3694	3694	3694	3694	3694	3694	3694	3694
	32.5	3498	3498	3498	3498	3498	3498	3498	3498	3498
	35	3269	3269	3269	3269	3269	3269	3269	3269	3269
	37.5	3037	3037	3037	3037	3037	3037	3037	3037	3037
	40	2812	2812	2812	2812	2812	2812	2812	2812	2812
	42.5	2629	2629	2629	2629	2629	2629	2629	2629	2629
	45	2480	2480	2480	2480	2480	2480	2480	2480	2480
	47.5	2352	2352	2352	2352	2352	2352	2352	2352	2352
50	2237	2237	2237	2237	2237	2237	2237	2237	2237	
52.5	2122	2122	2122	2122	2122	2122	2122	2122	2122	
55	1996	1996	1996	1996	1996	1996	1996	1996	1996	
57.5	1862	1862	1862	1862	1862	1862	1862	1862	1862	
60	1713	1713	1713	1713	1713	1713	1713	1713	1713	
62.5	1544	1544	1544	1544	1544	1544	1544	1544	1544	
65	1361	1361	1361	1361	1361	1361	1361	1361	1361	
67.5	1174	1174	1174	1174	1174	1174	1174	1174	1174	
70	988	988	988	988	988	988	988	988	988	
72.5	808	808	808	808	808	808	808	808	808	
75	627	627	627	627	627	627	627	627	627	
77.5	391	391	391	391	391	391	391	391	391	
80	234	234	234	234	234	234	234	234	234	
82.5	139	139	139	139	139	139	139	139	139	
85	80	80	80	80	80	80	80	80	80	
87.5	49	49	49	49	49	49	49	49	49	
90	32	32	32	32	32	32	32	32	32	



Report of Test

LLIA001589-001

Luminous Intensity (Candela) Table

		Lateral (C-Plane) Angles								
		0	22.5	45	67.5	90	112.5	135	157.5	180
Vertical (Gamma) Angles - Data was acquired in 0.5° increments, 2.5° increments shown.	90	32	32	32	32	32	32	32	32	32
	92.5	25	25	25	25	25	25	25	25	25
	95	21	21	21	21	21	21	21	21	21
	97.5	19	19	19	19	19	19	19	19	19
	100	18	18	18	18	18	18	18	18	18
	102.5	17	17	17	17	17	17	17	17	17
	105	16	16	16	16	16	16	16	16	16
	107.5	15	15	15	15	15	15	15	15	15
	110	14	14	14	14	14	14	14	14	14
	112.5	14	14	14	14	14	14	14	14	14
	115	14	14	14	14	14	14	14	14	14
	117.5	14	14	14	14	14	14	14	14	14
	120	14	14	14	14	14	14	14	14	14
	122.5	14	14	14	14	14	14	14	14	14
	125	14	14	14	14	14	14	14	14	14
	127.5	15	15	15	15	15	15	15	15	15
	130	15	15	15	15	15	15	15	15	15
	132.5	16	16	16	16	16	16	16	16	16
	135	16	16	16	16	16	16	16	16	16
	137.5	16	16	16	16	16	16	16	16	16
	140	16	16	16	16	16	16	16	16	16
	142.5	16	16	16	16	16	16	16	16	16
	145	16	16	16	16	16	16	16	16	16
	147.5	16	16	16	16	16	16	16	16	16
150	16	16	16	16	16	16	16	16	16	
152.5	16	16	16	16	16	16	16	16	16	
155	16	16	16	16	16	16	16	16	16	
157.5	15	15	15	15	15	15	15	15	15	
160	15	15	15	15	15	15	15	15	15	
162.5	14	14	14	14	14	14	14	14	14	
165	14	14	14	14	14	14	14	14	14	
167.5	13	13	13	13	13	13	13	13	13	
170	12	12	12	12	12	12	12	12	12	
172.5	10	10	10	10	10	10	10	10	10	
175	7	7	7	7	7	7	7	7	7	
177.5	5	5	5	5	5	5	5	5	5	
180	4	4	4	4	4	4	4	4	4	



Report of Test

LLIA001589-001

Coefficients of Utilization/Room Utilization - Zonal Cavity Method																						
Effective Floor Cavity Reflectance 0.20																						
RC	80					70					50				30				10			0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		101	101	101	99
1	109	105	101	97		106	102	99	95		98	95	92		94	91	89		90	88	86	84
2	100	92	85	79		97	90	84	78		86	81	76		83	78	75		79	76	73	71
3	91	81	73	66		88	79	72	66		76	70	64		73	68	63		70	66	62	60
4	83	72	63	56		81	70	62	56		68	61	55		65	59	54		63	58	53	51
5	77	64	55	49		74	63	55	48		61	53	48		59	52	47		57	51	47	44
6	71	58	49	43		69	57	48	42		55	47	42		53	46	41		51	46	41	39
7	66	52	44	38		64	52	43	37		50	43	37		48	42	37		47	41	36	35
8	61	48	39	34		60	47	39	33		46	38	33		44	38	33		43	37	33	31
9	57	44	36	30		56	43	35	30		42	35	30		41	34	30		40	34	30	28
10	54	41	33	27		52	40	32	27		39	32	27		38	32	27		37	31	27	25


For absolute test reports, RUs are expressed as a percentage of total lumen output. For relative test reports, CUs are expressed as a percentage of total lamp output. Calculations were based on published IES procedures, and are based on the zonal cavity method. Basic assumptions: 1) Room surfaces are lambertian reflectors. 2) Incident flux on each surface is uniformly distributed. 3) The room is spectrally neutral. When luminaires are not evenly distributed throughout the room, or do not exhibit lateral symmetry, CU values may differ from actual performance.

Circle of Light Plot				
Height(ft)	Illuminance at Nadir (fc)	Ground-level distance to half-of-nadir illuminance (ft)		
		0-180 deg	90-270 deg	
6.0	107.4	8.05	8.05	
8.0	60.4	10.73	10.73	
10.0	38.6	13.41	13.41	
12.0	26.8	16.10	16.10	
14.0	19.7	18.78	18.78	
16.0	15.1	21.46	21.46	

Spacing Criterion	
SC:	1.3

Average Luminance (cd/m ²)			
	0 deg Plane	45 deg Plane	90 deg Plane
0	140226	140226	140226
45	106553	106553	106553
55	98831	98831	98831
65	82521	82521	82521
75	50970	50970	50970
85	10369	10369	10369

Beam and Field Angle	
0-180 Degree Plane	
Beam Angle:	110.5°
Field Angle:	154.9°
90-270 Degree Plane	
Beam Angle:	110.5°
Field Angle:	154.9°



Report of Test

LLIA001589-001

UGR Table - Corrected

Reflectances

Ceiling Cavity	70	70	50	50	30	70	70	50	50	30
Walls	50	30	50	30	30	50	30	50	30	30
Floor Cavity	20	20	20	20	20	20	20	20	20	20

Room Size

UGR Viewed Crosswise

UGR Viewed Endwise


X=2H	Y=2H	27.2	28.8	27.6	29.1	29.5	27.2	28.8	27.6	29.1	29.5
	3H	28.7	30.2	29.1	30.5	30.9	28.7	30.2	29.1	30.5	30.9
	4H	29.2	30.5	29.6	30.9	31.3	29.2	30.5	29.6	30.9	31.3
	6H	29.3	30.5	29.7	30.9	31.3	29.3	30.5	29.7	30.9	31.3
	8H	29.3	30.5	29.7	30.9	31.3	29.3	30.5	29.7	30.9	31.3
	12H	29.3	30.4	29.7	30.8	31.3	29.3	30.4	29.7	30.8	31.3
4H	2H	27.8	29.1	28.2	29.5	29.9	27.8	29.1	28.2	29.5	29.9
	3H	29.4	30.6	29.9	31.0	31.4	29.4	30.6	29.9	31.0	31.4
	4H	30.0	31.0	30.4	31.4	31.9	30.0	31.0	30.4	31.4	31.9
	6H	30.1	31.0	30.6	31.5	31.9	30.1	31.0	30.6	31.5	31.9
	8H	30.1	31.0	30.6	31.4	31.9	30.1	31.0	30.6	31.4	31.9
	12H	30.1	30.9	30.6	31.4	31.9	30.1	30.9	30.6	31.4	31.9
8H	4H	30.1	30.9	30.6	31.4	31.9	30.1	30.9	30.6	31.4	31.9
	6H	30.3	31.0	30.8	31.5	32.0	30.3	31.0	30.8	31.5	32.0
	8H	30.3	30.9	30.8	31.4	31.9	30.3	30.9	30.8	31.4	31.9
	12H	30.3	30.8	30.8	31.4	31.9	30.3	30.8	30.8	31.4	31.9
12H	4H	30.1	30.8	30.6	31.3	31.8	30.1	30.8	30.6	31.3	31.8
	6H	30.3	30.9	30.8	31.4	31.9	30.3	30.9	30.8	31.4	31.9
	8H	30.3	30.8	30.8	31.3	31.9	30.3	30.8	30.8	31.3	31.9

Maximum UGR = 32.0




Report of Test LLIA001589-001

Iso-Illuminance Plot




The isofootcandle values shown in the plot above are based on a mounting height of $h = 8.0$ feet. Grid values show multiples of mounting height. The isoilluminance contour lines are expressed in units of footcandles. The values expressed are based on the direct light from a single unit without the contribution of room reflections.



Report of Test LLIA001589-001

Additional Pictures of Test Subject





Report of Test

LLIA001589-001

Test Distance 9.5 m
Ambient Temperature 25.1 °C

Notes

The laboratory has not participated in the selection of samples to be tested. All testing is performed on the understanding that the significance of the report is limited to the extent that the test sample is representative of production units.

Tested in accordance with the applicable sections of IES LM-79-19. Format of reports and angular increments based on IES LM-41-20 and LM-46-20.

The luminous intensity values, and other derived quantities, contained in this report are based on the absolute data, as measured.

Prorating the performance of the sample for the use of other component combinations (such as lamp / LED / Ballast / driver), or for use in different environmental conditions than that tested, may produce erroneous results.

This report is free of erasures and corrections.

Photometric intensity values are reported using the CIE C-Gamma coordinate system as defined in CIE publication number 121.

This report may contain data that are not covered by the NVLAP accreditation. Quantities marked with ‡ are not covered.

This report must not be used by the customer to claim product certification, approval or endorsement by NVLAP, NIST, or any agency of the Federal Government.