

# AL Compact 15kV NLEPR Insulation 133% IL AIA Black PVC Jacket. MV 105 - 50% Ground - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Three Conductor Aluminum, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, With 3 x Grounds Aluminum Interlocked Armor (AIA), Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compact stranded 8000 Series aluminum per ASTM B800 and ASTM B836
2. **Conductor Shield:** Semi-conducting cross-linked copolymer; A conductor separator is used for cable size larger than or equal to 500 Kcmil
3. **Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Three separate ground wires with a combined circular mil of 50% of the phase conductor. Class B compressed stranded bare copper per ASTM B3 and ASTM B8
7. **Filler:** Fillers as needed to make rounder
8. **Binder:** Polypropylene tape
9. **Armor:** Aluminum Interlocked Armor (AIA)
10. **Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure. Silicone Free

## SPECIFICATIONS:

- ASTM B801 Concentric-Lay-Stranded Conductors of 8000 Series Aluminum Alloy
- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

## SAMPLE PRINT LEGEND:

{SQFTG\_DUAL} SOUTHWIRE{R} POWER CABLE MASTER-DESIGN {UL} 3/C XXX KCMIL COMPACT AL. --- {ALUMAFLEX}{R} AA8176 220 MILS NL-EPR 15KV 133% INS LEVEL 25%TS GW 3 X X AWG CU MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL {NESC}

### Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Diameter Over armor	Jacket Thickness	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/Kcmil	No. of Strands	inch	inch	inch	No. x AWG	inch	mil	inch	lb/1000ft	lb	inch
TBA	1/0	19	0.336	0.814	0.874	3x10	2.253	75	2.403	2241	1900	16.8
TBA	2/0	19	0.376	0.854	0.914	3x8	2.339	75	2.489	2474	2395	17.4
TBA	3/0	19	0.422	0.900	0.960	3x8	2.438	75	2.588	2696	3020	18.1
671545	4/0	18	0.474	0.953	1.013	3x5	2.559	80	2.725	3265	3808	19.0
TBA	250	35	0.520	1.006	1.066	3x8	2.667	75	2.817	3230	4500	19.7
TBA	350	35	0.615	1.101	1.161	3x7	2.872	75	3.022	3811	6300	21.1
TBA	500	35	0.735	1.221	1.281	3x6	3.132	90	3.312	4723	9000	23.1
587887 <sup>^</sup>	750	53	0.908	1.426	1.486	3x1	3.581	90	3.769	6678	13500	26.3
575988	750	53	0.908	1.426	1.486	3x1	3.581	90	3.769	6672	13500	26.3

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

### Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0	0.168	0.211	0.046	0.044	0.584 + j0.394	0.211 + j0.043	2738	150/165	170/185
2/0	0.133	0.167	0.042	0.043	0.538 + j0.377	0.167 + j0.041	2862	170/185	190/215
3/0	0.105	0.133	0.039	0.041	0.501 + j0.358	0.133 + j0.04	3005	195/210	220/245
4/0	0.084	0.105	0.036	0.040	0.469 + j0.339	0.105 + j0.038	3166	220/240	255/285
250	0.071	0.090	0.034	0.039	0.45 + j0.321	0.09 + j0.037	3333	245/265	280/315
350	0.050	0.065	0.030	0.037	0.417 + j0.291	0.065 + j0.035	3628	295/315	345/385
500	0.035	0.046	0.026	0.035	0.386 + j0.26	0.046 + j0.033	3999	355/385	425/475
750	0.024	0.033	0.022	0.033	0.355 + j0.22	0.034 + j0.031	4566	440/475	540/600
750	0.024	0.033	0.022	0.033	0.355 + j0.22	0.034 + j0.031	4566	440/475	540/600

\* Ampacities are based on:

\* For Duct: Table 310.60(C)(80) Detail 1.

\* For Free Air: Table 310.60(C)(72).

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

\* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

\* Capacitive Reactance is between Phase-to-Shield.

