



Southwire™

RIGID CONDUIT BODIES

THREADED LB TYPE

FEATURES

- Threaded LB type
- NPT tapered hubs
- Suitable for use in concrete
- Suitable for use in wet locations

APPLICATION

- Provides access to conductors for pulling, splicing and maintenance

STANDARD MATERIAL

- Copper free aluminum die cast

STANDARD FINISH

- Powder coat


CERTIFICATIONS

- UL Standard: 514A
- Fed. Spec. W-C-586D
- NEMA FB 1



LB1

PART #	SIZE	WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
LB1	1/2"	1	6 AWG	10	100	28	4.295"	2.15"	1.33"
LB2	3/4"	2	6 AWG	10	50	19	5.09"	2.43"	1.54"
LB3	1"	3	6 AWG	5	25	18	5.915"	2.765"	1.74"
LB4	1-1/4"	3	2 AWG	2	10	13	7.894"	3.665"	2.49"
LB5	1-1/2"	3	2 AWG	2	10	14	7.894"	3.665"	2.49"
LB6	2"	3	2/0 AWG	1	5	13	10.134"	4.275"	3.10"
LB7	2-1/2"	3	2/0 AWG	---	1	3	12.50"	5.437"	4.45"
LB8	3"	3	4/0 AWG	---	1	4	12.50"	5.675"	4.45"
LB9	3-1/2"	3	400 MCM	---	1	7	15.50"	6.922"	5.50"
LB10	4"	3	400 MCM	---	1	7	15.50"	6.922"	5.50"



Rev. 0, 02/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.