

SHORT STACK MATERIAL LIFT

STANDARD FEATURES

- Lifts up to 800 lbs (360 kg)
- 12' 11" (3.9 m) and 16' 3" (4.9 m) heights
- No tools required, no loose hardware
- Mast hold-down secures mast for safe transport
- Sumner-built winch is highly reliable, single-speed winch uses idler roller to feed cable evenly on the drum to avoid cable flats and handles are removable when not in use
- Optional steering handle
- Optional fast action stabilizer legs are mounted on base top and stabilizer legs fold down with ease and lock in place
- 10" rough terrain wheels makes loading a truck or van hassle free
- Lockable 5" casters are hard tread urethane wheels
- Roller wheels help to roll into truck or vans
- Pulley guards designed to prevent load lines from slipping off
- Lifting eye is great for hoisting on/off vehicles
- Inside mast cable feed feeds cable inside mast, removing exposed cable from bear the operator's face



PART #	NET WEIGHT	LIFTING CAPACITY	HEIGHT STOWED	LENGTH STOWED	LENGTH OPERATING	BASE WIDTH	WIDTH WITH STABILIZER LEGS	GROUND CLEARANCE	LOAD HEIGHT	MAX HEIGHT	LOAD HEIGHT
2012S	320 lbs (145.1 kg)	800 lbs (362 kg)	63.5" (161.2 cm)	34" (86.3 cm)	62" (157.4 cm)	31.25" (79.3 cm)	74" (187.9 cm)	2.5" (6.3 cm)	6" (15.2 cm)	10' 11" (3.3 m)	12' 11" (3.9 m)
2016S	365 lbs (165.5 kg)	800 lbs (362 kg)	63.5" (161.2 cm)	34" (86.3 cm)	73" (185.4 cm)	31.25" (79.3 cm)	74" (187.9 cm)	2.5" (6.3 cm)	6" (15.2 cm)	14' 3" (4.3 m)	16' 3" (4.9 m)

SHORT STACK MATERIAL LIFT



PIPE CRADLE (#783705)

Great for duct pipe or other HVAC applications. Slides over standard forks. Packaged in sets of two.



FORK EXTENSIONS (#783691)

With the push of a button, forks may be extended from 28" to 42" (71–106 cm). With longer forks, the weight capacity decreases to 200 lbs (90 kg) and is clearly displayed on the forks when extended. A second button returns the extension for convenient storage inside the forks.

STEERING HANDLE (#786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.



BOOM CARRIAGE (#783642)

Ideal for installing pipe or lifting "from the top" applications. Uses four attaching plunger pins and has a 40" (100 cm) reach. Hook has five locations with load capacities of: 650 lbs (300 kg), 525 lbs (240 kg), 425 lbs (195 kg), 300 lbs (135 kg), and 200 lbs (90 kg).

TRAY (#786320)

Great for HVAC applications and positioning transformers and junction boxes. Steel tray slides onto forks.

TWO SPEED WINCH HANDLE (PART # 783759)

The two speed winch handle offers a standard speed setting or a high-speed setting for quick positioning of forks in half the time. Two handles needed per lift.