



Southwire™

MOGUL CONDUIT BODIES WITH COVER AND GASKET

LB TYPE WITH ROLLERS - HOT DIP GALVANIZED - MALLEABLE IRON

FEATURES

- c(UL)us wet locations
- Built in cable pulling roller
- Threaded NPT tapered hubs for Rigid and IMC conduit
- Smooth and round integral hub bushings protect conductor insulation
- Access to wiring for maintenance and future changes
- Assembled with raised cover, gasket and stainless steel cover screws

APPLICATION

- Use to pull straight or 90° angle turns or making taps and splices

- Provides long and large openings for pulling large conductors, splicing and taps
- Serve as a pull outlets for conductors that are stiff

STANDARD MATERIAL

- Body - Malleable iron
- Gasket - Neoprene rubber
- Screws - Stainless steel

STANDARD FINISH




- Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514A - UL 514D
- Fed. Spec: W-C-586D, A-A-50563
- NEMA: FB 1-2014 - NEMA 3R



MLB3CGHDG



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C	D	E	F
		MAX. NUMBER	MAX. SIZE									
MLB3CGHDG	1"	3	4 AWG	19	1	4	8.62"	5.98"	---	1.71"	2.19"	2.81"
MLB4CGHDG	1-1/4"	3	2 AWG	25	1	5	8.62"	5.98"	---	1.71"	2.19"	3.25"
MLB5CGHDG	1-1/2"	3	1/0 AWG	57	1	9	12.72"	10"	9.17"	2.26"	3.03"	3.63"
MLB6CGHDG	2"	3	4/0 MCM	75	1	13	12.72"	10"	9.17"	2.26"	3.03"	4.23"
MLB7CGHDG	2-1/2"	3	300 MCM	163	1	22	16.93"	15"	10.86"	3.41"	4.27"	5.22"
MLB8CGHDG	3"	3	350 MCM	211	1	38	16.93"	15"	10.86"	3.41"	4.27"	6.02"
MLB9CGHDG	3-1/2"	3	500 MCM	375	1	48	22.20"	19.96"	15.08"	4.28"	5.31"	6.71"
MLB10CGHDG	4"	3	500 MCM	439	1	59	22.20"	19.96"	15.08"	4.28"	5.31"	7.19"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.