

## SERIES 2100 MATERIAL LIFT

A versatile, inexpensive contractor lift.

### STANDARD FEATURES

- Lifts up to 650 lbs (300 kg)
- 12' (3.9 m), 18' (5.6 m), and 24' (7.2 m)
- Lightweight
- No loose hardware
- Available in optional galvanized finish (Part# 776270)



#### PULLEY GUARDS

LOAD CABLE CANNOT COME OFF

#### LOADING BAR

GREAT FOR OVERHEAD CRANES

#### ROLLER WHEELS

HELPS TO ROLL INTO TRUCKS OR VANS

#### SUMNER-BUILT WINCH

HIGHLY RELIABLE, SINGLE-SPEED WINCH USES IDLER ROLLER TO FEED CABLE EVENLY ON THE DRUM TO AVOID CABLE FLATS. HANDLES ARE REMOVABLE WHEN NOT IN USE.

#### INSIDE-MAST CABLE FEET

CABLE FEEDS INSIDE MAST, REMOVING EXPOSED CABLE FROM NEAR THE OPERATOR'S FACE

#### REVERSIBLE FORKS

USING PLUNGER PINS, FORKS REMOVE AND REVERSE EASILY FOR ADDED HEIGHT OR TO GET FLUSH WITH A CEILING. NO LOOSE PIECES.

#### 10" ROUGH TERRAIN WHEELS

MAKES LOADING A TRUCK OR VAN HASSLE FREE (OPTIONAL ON SERIES 2000 LIFTS)

#### LOCKABLE 5" CASTERS

HARD TREAD URETHANE WHEELS

#### FAST ACTION STABILIZER LEGS

MOUNTED ON BASE TOP, STABILIZER LEGS FOLD DOWN WITH EASE AND LOCK IN PLACE. (OPTIONAL ON MODELS 2010 & 2015)

PART #	DESCRIPTION	MAX HEIGHT	LIFTING CAPACITY	LIFT WEIGHT	SHIPPING WEIGHT
783650	2112 Contractor Lift	12' 11-3/8" (3.9 m)	650 lbs (300 kg)	252 lbs (114.5 kg)	287 lbs (130.5 kg)
783651	2118 Contractor Lift	18' 4-3/8" (4.9 m)	650 lbs (300 kg)	321 lbs (145.9 kg)	356 lbs (161.8 kg)
783652	2124 Contractor Lift	22' 9-3/8" (7.2 m)	650 lbs (300 kg)	366 lbs (166 kg)	399 lbs (181.4 kg)

## SERIES 2100 MATERIAL LIFT ACCESSORIES



### PIPE CRADLE (#783705)

Great for duct pipe or other HVAC applications. Slides over standard forks. Packaged in sets of two.



### FORK EXTENSIONS (#783691)

With the push of a button, forks may be extended from 28" to 42" (71–106 cm). With longer forks, the weight capacity decreases to 200 lbs (90 kg) and is clearly displayed on the forks when extended. A second button returns the extension for convenient storage inside the forks.



### BOOM CARRIAGE (#783642)

Ideal for installing pipe or lifting "from the top" applications. Uses four attaching plunger pins and has a 40" (100 cm) reach. Hook has five locations with load capacities of: 650 lbs (300 kg), 525 lbs (240 kg), 425 lbs (195 kg), 300 lbs (135 kg), and 200 lbs (90 kg).

### STEERING HANDLE (#786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.

PART #	DESCRIPTION
783882	Safety Brake - 2112
783883	Safety Brake - 2118
783884	Safety Brake - 2124

### SAFETY BRAKE

Each mast and carriage can have a factory installed, gravity actuated safety brake which holds loads in place to help avoid any slack in the cable.

### TWO SPEED WINCH HANDLE KIT (FACTORY INSTALLED PART # 783765)

The two speed winch handle offers a standard speed setting or a high speed setting for quickly positioning forks in half the time. Available only on Series 2100 lifts commencing with serial number 9433. For field installation kit, use part #783761.

PART #	HEIGHT STOWED	LENGTH STOWED	HEIGHT OPERATING	LENGTH OPERATING	BASE WIDTH	WIDTH W/ STABILIZER LEGS	GROUND CLEARANCE	LOAD HEIGHT (MINIMUM)	MAX HEIGHT (FORKS DOWN)	MAX HEIGHT (FORKS REVERSED)
2112	84" (2.13 m)	34" (0.86 m)	84" (2.13 m)	62" (1.57 m)	31-1/4" (0.80 m)	74" (1.88 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	10' 11-5/8" (3.3 m)	12' 11-3/8" (3.9 m)
2118	84" (2.13 m)	34" (0.86 m)	84" (2.13 m)	73" (1.84m)	31-1/4" (0.80 m)	74" (1.88 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	16' 4-5/8" (5 m)	18' 4-3/8" (5.6 m)
2124	84" (2.13 m)	34" (0.86 m)	84" (2.13 m)	73" (1.84m)	31-1/4" (0.80 m)	74" (1.88 m)	2-1/2" (6.4 cm)	6" (15.2 cm)	21' 9-5/8" (6.6 m)	23' 9-3/8" (7.2 m)