

# SERIES 2000 MATERIAL LIFT

## NEW MODELS! Model 2012S & 2016S Short Stack™ Material Lifts

- Lifts up to 800 lb (360 kg)
- 12' 11" (3.9 m) and 16' 3" (4.9 m) heights
- No tools required, no loose hardware
- Mast hold-down secures mast for safe transport

**Available in Optional Galvanized Finish!**

2012S - PN 784093  
2016S - PN 784086

### Pulley Guards

Designed to prevent load lines from slipping off

### Lifting Eye

Great for hoisting on/off vehicles

### Roller Wheels

Helps to roll into trucks or vans

### Inside Mast Cable Feed

Cable feeds inside mast, removing exposed cable from near the operator's face.

### Reversible Forks

Using plunger pins, forks remove and reverse easily for added height or to get flush with a ceiling. No loose pieces!


### \*\*\*Optional\*\*\* Steering Handle



Standard Position

### Sumner-built Winch

Highly reliable, single-speed winch uses idler roller to feed cable evenly on the drum to avoid cable flats. Handles are removable when not in use.



2012S shown here.  
PN 784094

2016S shown here.  
PN 784085

**Lockable 5" Casters**  
Hard tread urethane wheels.

### \*\*\*Optional\*\*\*Fast Action Stabilizer Legs

Mounted on base top, stabilizer legs fold down with ease and lock in place.

### 10" Rough Terrain Wheels

Makes loading a truck or van hassle free.



## Optional Features:

(Available in Optional Galvanized Finish - 2012S PN 784093 / 2016S PN 784086)



### Boom Carriage (PN 783642)

Ideal for installing pipe or lifting “from the top” applications. Uses four attaching plunger pins and has a 100 cm reach. Hook has five locations with load capacities of: 300 kg, 240 kg, 195 kg, 135 kg and 90 kg.



**NEW  
OPTION!**

### Tray (PN 786320)

Great for HVAC applications and positioning transformers and junction boxes. Steel tray slides onto forks.



### Fork Extensions (PN 783691)

With the push of a button, forks may be extended from 71–106 cm. With longer forks, the weight capacity decreases to 90 kg and is clearly displayed on the forks when extended. A second button returns the extension for convenient storage inside the forks.



**NEW  
OPTION!**

### Foot Jack (PN 784070)

Optional Foot Jack allows user to easily fold the legs of the lift up or down without laying the lift on it's back.



### Two Speed Winch Handle Kit (Factory Installed PN 783765)

The two speed winch handle offers a standard speed setting or a high speed setting for quickly positioning forks in half the time. Available only on Series 2100 lifts commencing with serial number 9433. For field installation kit, use PN 783761.



### Steering Handle (PN 786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.

Part #	Description
783881	Safety Brake Assembly

### Safety Brake

Each mast and carriage can have a factory installed, gravity actuated safety brake which holds loads in place to help avoid any slack in the cable.



### Pipe Cradle (PN 783705)

Great for duct pipe or other HVAC applications. Slides over standard forks. Packaged in sets of two.

## 2012S (784094) & 2016S (784085) Short Stack™ Material Lifts Specifications:

	2012S	2016S
<b>Net Weight</b>	320 lb / 145.1 kg	365 lb / 165.5 kg
<b>Lifting Capacity</b>	800 lb / 362 kg	800 lb / 362 kg
<b>Height Stowed</b>	63.5" / 161.2 cm	63.5" / 161.2 cm
<b>Length Stowed</b>	34" / 86.3 cm	34" / 86.3 cm
<b>Length Operating</b>	62" / 157.4 cm	73" / 185.4 cm
<b>Base Width</b>	31.25" / 79.3 cm	31.25" / 79.3 cm

	2012S	2016S
<b>Width w/Stabilizer Legs</b>	74.0" / 187.9 cm	74.0" / 187.9 cm
<b>Ground Clearance</b>	2.5" / 6.3 cm	2.5" / 6.3 cm
<b>Load Height (min)</b>	6.0" / 15.2 cm	6.0" / 15.2 cm
<b>Max Height (Forks Down)</b>	10'11" / 3.3 m	14'3" / 4.3 m
<b>Max Height (Forks Up)</b>	12'11" / 3.9 m	16'3" / 4.9 m