



# Southwire™

## SNAP-IN MC CABLE CONNECTORS

### SET SCREW TYPE WITH INSULATED THROAT

#### FEATURES

- No locknut required
- Single-unit or duplex construction with captive clamp

#### APPLICATION

- Use to join sheathed cable into outlet boxes or enclosures

#### STANDARD MATERIAL

- Steel

#### STANDARD FINISH

- Zinc plated

#### CERTIFICATIONS

- UL Standard: UL 514B
- Fed. Spec: W-F-406E




AMC1



AMC12



PART #	KO	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C
AMC1	1/2"	50	500	38	1.39"	.844"	.846"
AMC2	3/4"	25	250	48	1.63"	1.88"	.522"
AMC12	1/2"	25	250	14	1.52"	.916"	.868"



Rev. 0, 01/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



# Southwire™

## SNAP-IN MC CABLE CONNECTORS

### SET SCREW TYPE WITH INSULATED THROAT

PART #	KO SIZE	SIZE	CABLE TYPE	CABLE SIZE	OPENING MAX.	OPENING MIN.	WIRE BUNDLE DIAMETER MIN.	WIRE BUNDLE DIAMETER MAX.
AMC1	1/2"	MC-38S	AC STEEL	14-2 – 10-3	0.565"	0.475"	0.210"	0.330"
			AC STEEL HCF	14-2 – 10-3	0.565"	0.475"	0.220"	0.360"
			AC ALUMINUM	14-2 – 10-3	0.610"	0.464"	0.210"	0.330"
			AC ALUM HCF	14-2 – 10-3	0.610"	0.464"	0.220"	0.360"
			MCI STEEL	14-2 – 10-3	0.565"	0.455"	0.220"	0.360"
			MCI ALUMINUM	14-2 – 10-3	0.600"	0.455"	0.220"	0.360"
			MCI-A	14-2 – 10-3	0.510"	0.385"	0.220"	0.345"
			MCI-A HCF	14-2 – 10-3	0.510"	0.385"	0.240"	0.430"
			MC-PCS STEEL	12/2 - 12/3	0.610"	0.529"	0.360"	0.380"
			MC-PCS ALUMINUM	12/2 - 12/3	0.610"	0.529"	0.360"	0.380"
			FLEX CONDUIT	3/8"	0.610"	0.560"	---	---
AMC2	3/4"	MC-75S	AC STEEL	10-3 – 6-3	0.850"	0.545"	0.330"	0.500"
			AC STEEL HCF	10-3 – 6-3	0.850"	0.545"	0.360"	0.550"
			AC ALUMINUM	10-3 – 6-3	0.835"	0.600"	0.330"	0.500"
			AC ALUM HCF	10-3 – 6-3	0.835"	0.600"	0.360"	0.550"
			MCI STEEL	10-3 – 6-3	0.850"	0.550"	0.360"	0.550"
			MCI ALUMINUM	10-3 – 6-3	0.850"	0.580"	0.360"	0.550"
			MCI-A	8-3 - 6-3	0.785"	0.675"	0.460"	0.570"
			MCI-A HCF	8-3 - 6-3	0.785"	0.675"	0.510"	0.620"
			MC-PCS STEEL	8-3 - 6-3	0.679"	0.529"	0.510"	0.620"
			MC-PCS ALUMINUM	8-3 - 6-3	0.679"	0.529"	0.510"	0.620"
			FLEX CONDUIT	1/2"	0.920"	0.860"	---	---
AMC12*	1/2"	DMC-38S	AC STEEL	14-2 – 10-3	0.565"	0.475"	0.210"	0.330"
			AC STEEL HCF	14-2 – 10-3	0.565"	0.475"	0.220"	0.360"
			AC ALUMINUM	14-2 – 10-3	0.610"	0.464"	0.210"	0.330"
			AC ALUM HCF	14-2 – 10-3	0.610"	0.464"	0.220"	0.360"
			MCI STEEL	14-2 – 10-3	0.565"	0.455"	0.220"	0.360"
			MCI ALUMINUM	14-2 – 10-3	0.600"	0.455"	0.220"	0.360"
			MCI-A	14-2 – 10-3	0.510"	0.385"	0.220"	0.345"
			MCI-A HCF	14-2 – 10-3	0.510"	0.385"	0.240"	0.430"
			MC-PCS STEEL	12/2 - 12/3	0.610"	0.529"	0.360"	0.380"
			MC-PCS ALUMINUM	12/2 - 12/3	0.610"	0.529"	0.360"	0.380"
			FLEX CONDUIT	3/8"	0.610"	0.560"	---	---



AMC1



AMC12



\*Accepts 2 cables of each size listed.

Rev. 0, 01/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.