

SERIES 2400 CONTRACTOR LIFT

SUMNER

Sumner Manufacturing Co, Inc.

A Super Compact, Versatile Lift At A Great Price!

Series 2400 Features:

- ✓ Super Compact 12 ft (3.7 m) & 16 ft (4.9 m) lifts
- ✓ 450 lbs (200 kg) lift capacity
- ✓ One piece construction –no loose pieces
- ✓ Easily portable for one person operation
- ✓ Fits most SUVs and vans
- ✓ 12' 11-3/4" & 16' 11-3/8" heights when forks reversed

The Perfect Lift For ...

- ▶ HVAC Contractors
- ▶ Electrical Contractors
- ▶ Industrial Maintenance
- ▶ Steel Erectors
- ▶ Facility Management

Pulley Guards

Contains load cable ... line cannot come off.

Handle

Use convenient handle for "hand truck" mobility and to position lift at point of use.

Winch

Coffee grinder style winch features auto-braking and detachable winch handles.

Roller Wheels

Handy wheels located to ease rolling into vehicles for transportation.

8" (20 cm) non-marring wheels



Reversible Forks

Two plunger pins permit quick release of forks. Forks may be removed for storage or reversed for added height.

Inside-Mast Cable Feed

Cable feeds inside mast, removed from the operator for safety – similar to the 2000 and 2100 Series lifts.



Series 2400 Contractor Lift	2412		2416	
Part No.	784750		784751	
Height Max (forks up)	12' 11-3/4"	4.0 m	16' 11-3/8"	5.2 m
Height Max (forks down)	12'	3.7 m	15' 11-5/8"	4.9 m
Lift Capacity	450 lbs	200 kg	450 lbs	200 kg
Height Stowed	62-3/4"	159.4 cm	62-3/4"	159.4 cm
Length Stowed	23"	58.4 cm	23"	58.4 cm
Length Operating	48"	121.9 cm	48"	121.9 cm
Width Stowed	26-3/8"	67.1 cm	26-3/8"	67.1 cm
Width Max	26-3/8"	67.1 cm	55-1/4"	140.3 cm
Winch Cranks per ft/m	8/ft	24/m	8/ft	24/m
Basic Weight	195 lbs	88.5 kg	243 lbs	110.2 kg

Double Row Casters

- ✓ Four 3" (7.5 cm) casters permit easy handling of heavy loads
- ✓ Swivel independently
- ✓ Lockable to insure safety
- ✓ Allow for multi-directional positioning of lift

 MADE IN USA

SERIES 2400 CONTRACTOR LIFT


Ideal for Compact Storage

No tools or loose hardware to worry about. Leg lock mechanism releases with plunger pin and slides on base leg.

Leg roller allows unit to wheel in stored position.

Compact Storage

Forks remove and legs reposition for space saving storage.



SERIES 2400 OPTIONS ...




Fork Extension (part no. 784695)

With the push of a button, forks may be extended from 23-1/4" (59.2 cm) to 29-7/16" (75.7 cm). When using the fork extensions the weight capacity reduces to 200 lbs (90 kg), as is clearly marked on the extended forks. A second button returns the extension for storage inside forks.

Tray (part no. 784320)

24" x 28"
(61 x 71 cm)
steel tray
slides
onto forks.



Pipe Cradle (part no. 783705)

Great for
air ducts or
other HVAC
applications.
Slides over
forks. Packaged
two per set.



Cable Brake (part no. 784755)

Each mast and carriage can have a factory installed, gravity actuated safety brake which holds loads in place in the event cable goes slack.

SUMNER

Sumner Manufacturing Co, Inc.
www.sumner.com

DISTRIBUTED BY:

Sumner - U.S. 7514 Alabonson Road • Houston, TX 77088 • Ph: 281-999-6900 • Fax: 281-999-6966

Sumner - Canada 75 Saltsman Drive, Unit 5 • Cambridge, Ontario N3H 4R7 • Ph: 519-653-5300 • Fax: 519-653-5305

Sumner - Netherlands Midden Engweg 21 • NL-3882TS Putten • The Netherlands • Ph: +31 (0) 85 489 0284 • europesales@sumner.com

Sumner - U.K. Unit 3 Kempton Road • Keytec 7 Business Park • Pershore, Worcestershire WR10 2TA • Ph: (44) 01386 556278 • Fax: (44) 01386 556776