



REEL MAC THE REAL JACK

Sumner brings you the best built, best value reel jack you can buy. Reel Mac jacks are available in two styles. Style numbers 60 and 70 feature screw-type adjustment with large 1-1/2" screws and large, easy to use handles.

Reel Mac Reel Jack Features:

- All Steel Construction
- Rugged Design for Job Site Use
- Dependable Sumner Quality



No. 60 (Part # 780941)
Screw-type Telescoping
Reel Jack for 26 to 56"
diameter reels.



No. 70 (Part # 780942)
Screw-type Telescoping
Reel Jack for 46 to 96"
diameter reels.




No. 80 (Part # 780943)
Heavy Duty Ratchet
Drive Reel Jack for
reels up to 90" in
diameter. Convenient,
detachable ratchet
handle stores in base
when not in use.

Part #	Description	Height Range		Load Capacity		Use with Spindle	Weight	
		inches	cm	lb	kg		lb	kg
780941	Reel Mac No. 60	13 - 27"	33 - 68 cm	2,500	1,135	61	30	13.6
780942	Reel Mac No. 70	21 - 54"	53 - 137 cm	2,500	1,135	71	51	23.1
780943	Reel Mac No. 80	28 - 45"	71 - 114 cm	3,750	1,700	81	105	47.6

Reel Mac Spindles

Sumner spindles are designed to be used with Reel Mac reel jacks. See the chart below to select the right spindle for you needs.



Spindle #	Part #	Diameter		Load Capacity		Use with Reel Mac	Weight	
		inches	cm	lb	kg		lb	kg
61	780229	2-3/8"	6.0 cm	5,000	2,270	60	37	16.8
71	780230	2-3/8"	6.0 cm	5,000	2,270	70	47	21.3
81	780231	3-1/2"	8.9 cm	7,500	3,400	80	118	53.5