

LED A19 LAMP ANTIQUÉ FILAMENT



SUGGESTED APPLICATIONS

- Replacement for traditional incandescent lighting
- Residential, commercial, retail, restaurants, hospitality
- Decorative lighting, wall sconces, chandeliers

FEATURES

- The LED A19 filament lamp provides energy savings with a decorative, vintage style
- Up to 85% energy savings compared to incandescent lamps
- Suitable for enclosed fixtures
- Available in 2700K CCT with clear glass or 2200K CCT with amber glass



LED A19 Lamp ANTIQUE FILAMENT

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120V, 50/60Hz	Functional Life (L70): 15,000 hours
Input Current: 85mA	Location Rating: Damp
Power Factor: <0.7	Ambient Operating Temperature: -4°F to 104°F
Dimmable: Phase cut, down to 10%	Enclosed Fixture Rated
Efficacy: Up to 100 LPW	Housing Construction: Aluminum base
Minimum CRI: 80	Base: E26
Beam Angle: 280°	Lens Type: Glass

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	Lumens	Wattage	CCT	Finish/Color
LA19-8W-822-ANTQ	73287	650	8W	2200K	Amber
LA19-8W-827-ANTQ	73289	800	8W	2700K	Clear

NOMENCLATURE


LA19=Lamp A19 Shape - 8W=8 Watt - 822 = 80 CRI 2200K CCT - ANTQ = Antique Filament Style
 - 828 = 80 CRI 2700K CCT

ENERGY SAVINGS

Catalog Number	LED Lamp Wattage	Incandescent Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
LA19-8W-822-ANTQ	8W	60W	52W	\$25	\$125
LA19-8W-827-ANTQ	8W	60W	52W	\$25	\$125

DIMENSIONS/WEIGHTS

Catalog Number	(A)	(B)	Weight
LA19-8W-822-ANTQ	3.90"	4.3"	0.08 Lbs.
LA19-8W-827-ANTQ	3.90"	4.3"	0.08 Lbs.



NOTES

Dimming - This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 10%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.topaz-usa.com/led-dimmer-compatibility for up-to-date dimmer compatibility information. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

THREE (3) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC: For details visit: www.topaz-usa.com/warranty
 Not for Sale in California
 Specifications subject to change without prior notice. Replacement wattage shown depends on application and fixture.