


**Crossing TW-TW, adjustable, KUMAX, 55°–90°, for contact wire 100 mm<sup>2</sup> - 120 mm<sup>2</sup>**  
**Part no. B1180-01**



**Technical data**

Dimensions

A: 1902 mm

Material and weight

Weight: 18.000 kg

Loads and tightening torque

-

Standards applied

-

Function

-

Specifications

-

Spare parts

-

Accessories

-

Comments

- For use with flat and bowed pantographes
- It is recommendet to use the special installation tool part no. WD2725-01
- Contact wire reinforcing run-out side part no. C1996-01
- Jig to check the runner wear (check prism) part no. WE3513-01
- Special applications for double crossings on request
- Spare material
- Mid piece for crossing TWpart no. D2716-01 (for B1180-01 and B1180-02)
- Glider for crossing TW-TW part no. D2715-01 (for B1180-01) andpart no. D2715-02 (for B1180-02)



**Southwire™**



**A COLAS RAIL COMPANY**

**Contact Us: [Transit@southwire.com](mailto:Transit@southwire.com)**