


RIGID LR BODIES

Southwire® SIMPush™ Rigid conduit bodies are used as junction or pull boxes and are usually installed in an a threaded or non-threaded, RMC, IMC, GRC, ARC and rigid stainless-steel conduit system to facilitate a change in direction.

FEATURES:

- Corrosion-resistant copper-free diecast aluminum construction
- Raintight to prevent water from getting into conduit, box, or enclosure
- IP66 – Dust tight and protects against powerful jetting water
- Concrete-tight
- Provides continuous ground
- Powder-coated externally for corrosion resistance
- Internally coated with lubricating grease
- Tested to 100 removal cycles for reuse
- Locking teeth are constructed from zinc-plated steel
- Works with threaded or unthreaded conduit



TO REMOVE THE SIMPush™ FITTING, SIMPLY SLIDE THE REMOVAL TOOL ONTO THE COLLAR AND PULL


1/2" – 1-1/2"



CERTIFICATIONS/RATINGS:
NEMA FB RATED (4X)
E-FILE #: E474806



RMCLR050, RMCLR075, RMCLR100, RMCLR125, RMCLR150



Stock #	Model #	Trade Size	Quantity Per Box	H (in.) A	W (in.) B	L (in.) C	Associated Removal Tool Model #	Removal Tool Included
CONTRACTOR PACK								
65081502	R-LR-050W	1/2"	4	5.34	2.83	1.4	R-RT-P1	-
65081602	R-LR-075W	3/4"	4	6.11	3.09	1.64	R-RT-P1	-
65081702	R-LR-100W	1"	4	6.99	3.33	1.9	R-RT-P2	-
65081802	R-LR-125W	1-1/4"	3	9.02	4.53	2.85	R-RT-P2	-
65081902	R-LR-150W	1-1/2"	3	9.05	4.56	2.85	R-RT-P3	-

Project Name:
Contractor:
Address:

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.