



LED A19 LAMP PERFORMANCE

SUGGESTED APPLICATIONS

- Fan lights, decorative, recessed, task lighting
- Residential, hospitality, retail, restaurants, commercial

FEATURES

- 90 CRI provides exceptional color rendering
- T20: Can be used to comply with California Energy Commission's Lighting Appliance Efficiency Regulations
- T24 JA8: Select models can be used to comply with California Energy Commission's High Efficacy LED light source requirements
- Dimmable down to 10% of total light output
- Up to 85% energy savings



INPUT VOLTAGE: 120V

FREQUENCY: 60Hz

**POWER FACTOR, THD%:
>0.9, <20%**

DIMMABLE: 100% TO 10%


EFFICACY: UP TO 92 LPW

CRI: 90

BEAM ANGLE: 230°

**LIFETIME (L70):
UP TO 15,000 HOURS**

**ENCLOSED FIXTURE RATING:
NOT SUITABLE FOR ENCLOSED
FIXTURES**



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



LED A19 LAMP PERFORMANCE

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	ORDER CODE	UPC	LUMENS	WATTAGE	INPUT CURRENT	CCT	CBCP (CD)
LA19/12W/927/D-33	70989	751338037724	1,100	12W	110mA	2700K	136
LA19/12W/930/D-33	70992	751338037731	1,100	12W	110mA	3000K	139
LA19/12W/940/D-33	70994	751338037748	1,100	12W	110mA	4000K	145
LA19/12W/950/D-33	70996†	751338037755	1,100	12W	110mA	5000K	145

† Not for sale in residential new construction in California.

ORDERING GUIDE

Example: LA19/12W/927/D-33


PRODUCT	WATTAGE	CRI	OPTIONS
LA19 = LAMP A19	12W	927 = 90 CRI AND 2700K 930 = 90 CRI AND 3000K 940 = 90 CRI AND 4000K 950 = 90 CRI AND 5000K	D = DIMMABLE

ENERGY SAVINGS *Based on 12 hours/day and \$0.11/kWh*

MODEL #	LED WATTAGE	INCANDESCENT REPLACEMENT WATTAGE	WATTS SAVED	YEARLY SAVINGS	5 YEAR SAVINGS
LA19/12W/9xx/D-33	12W	75W	63W	\$30	\$152

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	WEIGHT (LBS.)
LA19/12W/9xx/D-33	4.41	2.36	0.11



NOTES

Dimming- This product is designed to be compatible with most leading-edge type incandescent and LED style dimmers. (Dimming range 100% down to 10%). Product performance may vary depending on dimmer manufacturer and circuit loading. Visit www.southwire.com or contact your local Southwire representative for a list of compatible dimmers.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.



800-666-2852 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.