


3/C CU 15KV 220 NL-EPR 133% TS GSIA PVC MV-105

Type MV-105 Three Conductor Copper, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Galvanized Steel Interlocked Armor (GSIA), Polyvinyl Chloride (PVC) Jacket



Images not to scale. See Table 1 for Dimensions

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
- Conductor Shield:** Semi-conducting cross-linked copolymer
- Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
- Insulation Shield:** Stripable semi-conducting cross-linked copolymer
- Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
- Grounding Conductor:** 1 Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8
- Filler:** Wax paper filler
- Binder:** Polypropylene tape
- Armor:** Galvanized Steel Interlocked Armor (GSIA)
- Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or annealed copper
- ASTM B8 Concentric-lay-standard copper
- UL 1072 - Medium Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable & ICEA S-97-682 5-46 KV Utility
- UL 1685/FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 -Flame Test (70,000) BTU/hr Vertical Tray Test
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTNING BOLT] #P# (UL) 3/C [#AWG or #kcmil] CU 220 MILS NL-EPR GSIA 15KV 133% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL FT4 YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire[®]

Table 1 – Weights & Measurements

Stock Code	Cond. Size AWG	Diameter over			Ground No. x AWG	Dia. Over Armor (9) inches	Jacket Thickness mils	Approx. OD (10) inches	Approx. Weight lbs./MFT	Max Pull Tension lbs.	Min Bending Radius inches
		Cond. (1) inches	Insul. (3) inches	Insul. Shield inches							
610105	2	0.283	0.760	0.820	1 x 6	2.036	60	2.156	2810	1593	15.1
TBA	1	0.322	0.799	0.859	1 x 4	2.121	60	2.241	3132	2009	15.7
TBA	1/0	0.362	0.839	0.899	1 x 4	2.207	60	2.327	3463	2534	16.3
581972	2/0	0.405	0.882	0.942	1 x 4	2.300	75	2.450	3925	3194	17.1
TBA	3/0	0.456	0.933	0.993	1 x 3	2.410	75	2.560	4452	4027	17.9
TBA	4/0	0.512	0.989	1.049	1 x 3	2.531	75	2.681	5048	5078	18.8
TBA	250	0.558	1.044	1.104	1 x 3	2.650	75	2.800	5589	6000	19.6
611038	350	0.661	1.147	1.207	1 x 2	2.872	75	3.022	6918	8400	21.2
581973	500	0.789	1.275	1.335	1 x 1	3.149	85	3.319	8879	12000	23.2
TBA	750	0.968	1.463	1.523	1 x 0	3.555	85	3.725	11961	18000	26.1

All dimensions are nominal and subject to normal manufacturing tolerances

Table 2 – Electrical and Engineering Data

Stock Code	Cond. Size AWG	Resistance		Reactance		Positive Sequence Impedance*	Zero Sequence Impedance*	Shield Short Circuit Current 6 Cycles Amps	Allowable Ampacities 90°C/105°C	
		DC @ 25°C	AC @ 90°C	X _C @ 60Hz	X _L @ 60Hz				Directly Buried †	In Air ‡
		Ω/MFT	Ω/MFT	MΩ*MFT	Ω/MFT				Amps	Amps
610105	2	0.162	0.203	0.053	0.047	0.203 + j0.047	0.577 + j0.419	2700	185 / 200	165 / 185
TBA	1	0.129	0.161	0.049	0.045	0.162 + j0.045	0.535 + j0.401	2827	210 / 225	185 / 210
TBA	1/0	0.102	0.128	0.045	0.043	0.128 + j0.043	0.499 + j0.383	2957	240 / 255	215 / 240
581972	2/0	0.081	0.101	0.042	0.042	0.102 + j0.042	0.471 + j0.366	3097	270 / 290	245 / 275
TBA	3/0	0.064	0.081	0.039	0.040	0.081 + j0.040	0.446 + j0.346	3263	305 / 330	285 / 315
TBA	4/0	0.051	0.064	0.036	0.039	0.065 + j0.039	0.426 + j0.327	3445	350 / 375	325 / 360
TBA	250	0.043	0.054	0.034	0.038	0.055 + j0.038	0.411 + j0.309	3624	380 / 410	360 / 400
611038	350	0.031	0.039	0.030	0.036	0.040 + j0.036	0.386 + j0.279	3959	460 / 495	435 / 490
581973	500	0.022	0.028	0.026	0.034	0.028 + j0.034	0.362 + j0.247	4376	550 / 590	535 / 600
TBA	750	0.014	0.020	0.022	0.032	0.020 + j0.032	0.335 + j0.209	4987	665 / 720	670 / 745

* Calculations are based on 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(83) of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(71) of the 2014 National Electrical Code (40°C Ambient Air Temperature)

