



Southwire™

RIGID WATERTIGHT HUBS

WITH BONDING SCREW - ZINC DIE CAST

FEATURES

- Raintight, oiltight, and dust tight
- Flame-retardant insulated throat
- Oversized locknut protects against damage from vibrations and promotes positive grounding

APPLICATION

- Indoor or outdoor use
- Use to connect Rigid or IMC conduit to a load center or other metal enclosure where a watertight joint is required at knockouts or slip-fit holes

STANDARD MATERIAL

- Zinc die cast

CERTIFICATIONS


- NEMA 2, 3R, 4, 4X, 5, 12, 13



201B



PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	MAX. COPPER WIRE SIZE UL#
201B	1/2"	25	250	53	1.31"	1.54"	#8
202B	3/4"	10	100	30	1.37"	1.73"	#8
203B	1"	10	100	43	1.59"	2.04"	#8
204B	1-1/4"	2	20	12	1.59"	2.42"	#8
205B	1-1/2"	2	20	15	1.59"	2.79"	#8
206B	2"	2	20	10	1.59"	3.30"	#8
207B	2-1/2"	---	2	8	2.44"	3.70"	#6
208B	3"	---	2	10	2.44"	4.39"	#6
209B	3-1/2"	---	1	13	2.44"	4.88"	#6
210B	4"	---	1	15	2.44"	5.50"	#4



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.