


1/C COMPACT CU 5KV 115 NL-EPR 133% Or 8KV 100% TS SIMpull® PVC MV-105

Type MV-105 Single Conductor Compact Copper, 5kV/8kV 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133%/100% Insulation Level, Tape Shield, SIMpull® Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Images not to scale. See Table 1 for Dimensions

CONSTRUCTION:

1. **Conductor:** Class B compact stranded per ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer;
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Stripable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 5KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B496 - Compact Round Concentric-lay-standard copper
- UL 1072 - Medium Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable & ICEA S-97-682 5-46 KV Utility
- UL 1685/FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 AWG and Larger)
- IEEE 1202 -Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 AWG and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- CSA C68.10 - Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C22.2 No.230 - Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 - Cable Test Methods

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTNING BOLT] #P# (UL/CSA) 1/C [#AWG or #kcmil] CU 115 MILS NL-EPR 5KV 133%/ 8KV 100% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. TC-ER(CSA 1/0 LARGER) FOR DIRECT BURIAL FT4 -ST1 YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire®

Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Table 1 – Weights & Measurements

Stock Code	Cond. Size AWG	Diameter over			Jacket Thickness ¹ mils	Approx. OD (6) inches	Approx. Weight lbs./MFT	Max Pull Tension lbs.	Min Bending Radius inches	Conduit Size* inches
		Cond. (1)	Insul. (3)	Insul. Shield						
		inches	inches	inches						
TBA	2	0.268	0.535	0.595	65	0.745	445	531	8.9	2.5
TBA	1	0.299	0.566	0.626	65	0.776	512	670	9.3	2.5
TBA	1/0	0.336	0.603	0.663	65	0.813	597	845	9.8	2.5
TBA	2/0	0.376	0.643	0.703	65	0.853	700	1065	10.2	2.5
TBA	3/0	0.423	0.690	0.750	80	0.930	854	1342	11.2	3
TBA	4/0	0.475	0.742	0.802	80	0.982	1013	1693	11.8	3
TBA	250	0.520	0.796	0.856	80	1.036	1156	2000	12.4	3
TBA	350	0.616	0.892	0.952	80	1.132	1509	2800	13.6	3.5
TBA	500	0.736	1.012	1.072	80	1.252	2026	4000	15.0	3.5
679723	750	0.908	1.215	1.275	80	1.455	2873	6000	17.5	4
TBA	1000	1.060	1.367	1.427	80	1.607	3701	8000	19.3	5

All dimensions are nominal and subject to normal manufacturing tolerances

* Conduit size based on 3 phase 40% fill-factor without ground

¹ Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 2 – Electrical and Engineering Data

Stock Code	Cond. Size AWG	Resistance		Reactance		Positive Sequence Impedance*	Zero Sequence Impedance*	Shield Short Circuit Current 6 Cycles Amps	Allowable Ampacities 90°C/105°C	
		DC @ 25°C	AC @ 90°C	X _C @ 60Hz	X _L @ 60Hz				In Duct †	In Air ‡
		Ω/MFT	Ω/MFT	MΩ*MFT	Ω/MFT				Amps	Amps
TBA	2	0.162	0.203	0.037	0.045	0.335 + j0.045	0.698 + j0.521	1968	145 / 155	190 / 215
TBA	1	0.129	0.161	0.034	0.044	0.266 + j0.044	0.632 + j0.503	2069	170 / 180	225 / 250
TBA	1/0	0.102	0.128	0.032	0.042	0.212 + j0.042	0.580 + j0.482	2189	195 / 210	260 / 290
TBA	2/0	0.081	0.101	0.029	0.041	0.168 + j0.040	0.538 + j0.461	2320	220 / 235	300 / 330
TBA	3/0	0.064	0.081	0.026	0.040	0.133 + j0.040	0.503 + j0.437	2473	250 / 270	345 / 385
TBA	4/0	0.051	0.064	0.024	0.038	0.106 + j0.038	0.476 + j0.413	2642	290 / 310	400 / 445
TBA	250	0.043	0.054	0.023	0.038	0.090 + j0.037	0.459 + j0.390	2817	320 / 345	445 / 495
TBA	350	0.031	0.039	0.020	0.036	0.064 + j0.036	0.429 + j0.353	3130	385 / 415	550 / 615
TBA	500	0.022	0.028	0.017	0.034	0.046 + j0.034	0.402 + j0.312	3520	470 / 505	695 / 775
679723	750	0.014	0.020	0.016	0.033	0.031 + j0.032	0.369 + j0.257	4180	585 / 630	900 / 1000
TBA	1000	0.011	0.016	0.014	0.031	0.024 + j0.031	0.347 + j0.224	4675	670 / 720	1075 / 1200

* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(69) of the 2014 National Electrical Code (40°C Ambient Air Temperature)

