



**Southwire™**

# SNAP-IN CONNECTORS

## DOUBLE SNAP LOCK - ZINC

### FEATURES

- Easy to install
- Labor savings by simply snap the fitting into the knockout hole
- Snap-In design
- No tools are required
- Integrated anti-short bushing
- Not suitable for PVC jacketed/coated cables
- Wide variety of cables

### APPLICATION

- Indoor use only
- In a dry location
- Use to connect steel to a steel outlet box or other metal enclosure

### STANDARD MATERIAL

- Zinc die cast

### CERTIFICATIONS

- cULus



38ASTSW

40ASTSW



PART #	SIZE	KO	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	HEIGHT	WIDTH	LENGTH
38ASTSW	3/8"	1/2"	50	500	2.8	1.41"	1"	1"
40ASTSW	3/8"	1/2"	50	500	2.8	1.41"	1"	1"

Rev. 0, 01/25

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2025 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

# SNAP-IN CONNECTORS

## DOUBLE SNAP LOCK - ZINC

### APPROVED CABLES

PART #	SIZE	KO	CABLE TYPE	CONDUIT, SIZE/ CABLE, AWG	CABLE DIAMETER RANGE (IN)
38ASTSW	3/8	1/2	AC CABLE, ALUMINUM	14/2 – 10/3	0.405 – 0.612
			AC CABLE, STEEL	14/2 – 10/3	0.451 – 0.593
			METAL CLAD CABLE, MCI-A, STEEL	14/2 – 10/3	0.451 – 0.593
			METAL CLAD CABLE, MCI-A, ALUMINUM	14/2 – 10/3	0.439 – 0.58
			FMC, STEEL	3/8"	0.56 – 0.61
			FMC, ALUMINUM	3/8"	0.56 – 0.61
			RWFMC, STEEL	3/8"	0.56 – 0.61
			RWFMC, ALUMINUM	3/8"	0.56 – 0.61
			METAL CLAD CABLE, MCC, ALUMINUM	14/2 – 10/3	0.451 – 0.593
			HCF ARMORED CABLE, STEEL	12/2 – 10/3	0.470 – 0.610
			HCF ARMORED CABLE, ALUMINUM	14/2 – 10/3	0.402 – 0.610
40ASTSW	1/2	1/2	AC CABLE, ALUMINUM	14/3 – 10/3	0.485 – 0.612
			AC CABLE, STEEL	14/3 – 10/3	0.464 – 0.58
			METAL CLAD CABLE, MCI-A, STEEL	14/3 – 10/3	0.464 – 0.593
			METAL CLAD CABLE, MCI-A, ALUMINUM	14/3 – 10/3	0.464 – 0.593
			FMC, STEEL	3/8"	0.56 – 0.61
			FMC, ALUMINUM	3/8"	0.56 – 0.61
			RWFMC, STEEL	3/8"	0.56 – 0.61
			RWFMC, ALUMINUM	3/8"	0.56 – 0.61
			METAL CLAD CABLE, MCC, ALUMINUM	14/3 – 10/3	0.464 – 0.593
			HCF ARMORED CABLE, STEEL	12/2 – 10/3	0.470 – 0.610
			HCF ARMORED CABLE, ALUMINUM	14/2 – 10/3	0.402 – 0.610

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.