



Southwire™

RIGID COUPLINGS

SET SCREW TYPE - HOT DIP GALVANIZED - MALLEABLE IRON

FEATURES

- Set screw type coupling
- Concrete tight when taped
- Hot dip galvanized for added durability and corrosion protection

APPLICATION

- Use to join two unthreaded lengths of Rigid conduit or IMC

STANDARD MATERIAL

- Malleable iron
- Galvanized steel screw

STANDARD FINISH

- Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514B
- RoHS
- Fed. Spec: W-F-406E, W-F-406D
- NEMA: FB 1




681MHDG



Conforms to finish thickness
ASTM A123/123M

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B
681MHDG	1/2"	---	25	7	1.77"	1.17"
682MHDG	3/4"	---	25	10	1.96"	1.39"
683MHDG	1"	---	25	16	2.69"	1.66"
684MHDG	1-1/4"	5	50	41	2.73"	2.01"
685MHDG	1-1/2"	4	40	42	3.19"	2.25"
686MHDG	2"	---	20	28	3.40"	2.75"



Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.