

15kV CU 100% TRXLPE Full Neutral LLDPE Primary UD

Single Conductor, 175 Mils Tree Retardant Cross Linked Polyethylene, 100% Insulation Level, Full Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Non Moisture Blocked Optional)
- Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
- Insulation:** 175 Mils Tree Retardant Cross Linked Polyethylene 100% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Concentric Neutral:** Helically applied soft drawn bare copper full concentric neutral
- Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 15kV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- UL 1072 - Listed Listed as MV 90 When Specified

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 15000 VOLTS TRXLPE INSULATION 175 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire

**CABLETECH
SUPPORT™**

Services

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension*
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb /1000ft	inch	lb
TBA	2 (1)	0.258	0.645	175	0.725	16x14	0.164	50	0.953	654	11.4	531
TBA	2 (7)	0.283	0.670	175	0.750	16x14	0.164	50	0.978	679	11.7	531
TBA	1 (1)	0.289	0.676	175	0.756	13x12	0.128	50	1.016	794	12.2	670
TBA	1 (19)	0.322	0.709	175	0.789	13x12	0.128	50	1.049	826	12.6	670
TBA	1/0 (1)	0.325	0.712	175	0.792	16x12	0.104	50	1.052	931	12.6	845
TBA	1/0 (19)	0.362	0.749	175	0.829	16x12	0.104	50	1.089	968	13.1	845
TBA	2/0 (19)	0.405	0.792	175	0.872	13x10	0.080	50	1.176	1191	14.1	1065
TBA	3/0 (19)	0.456	0.843	175	0.923	16x10	0.065	50	1.227	1413	14.7	1342
TBA	4/0 (19)	0.512	0.899	175	0.979	16x9	0.052	50	1.308	1720	15.7	1693
TBA	250 (37)	0.558	0.954	175	1.034	25x10	0.042	50	1.338	1986	16.1	2000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C†	Allowable Ampacity Directly Buried 90°C‡
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (1)	0.162	0.203	0.053	0.049	0.163	0.423	0.364+j0.071	0.206+j0.048	5856.3	155	195
2 (7)	0.162	0.203	0.050	0.047	0.172	0.447	0.364+j0.070	0.206+j0.047	5856.3	155	195
1 (1)	0.129	0.161	0.050	0.048	0.174	0.453	0.290+j0.057	0.164+j0.047	7560.0	175	220
1 (19)	0.129	0.161	0.046	0.046	0.187	0.486	0.290+j0.056	0.164+j0.046	7560.0	175	220
1/0 (1)	0.102	0.128	0.046	0.046	0.188	0.489	0.235+j0.047	0.132+j0.045	9304.6	200	250
1/0 (19)	0.102	0.128	0.043	0.045	0.202	0.525	0.235+j0.046	0.132+j0.044	9304.6	200	250
2/0 (19)	0.081	0.101	0.040	0.044	0.218	0.567	0.183+j0.039	0.106+j0.042	12017.3	225	285
3/0 (19)	0.0642	0.081	0.037	0.043	0.237	0.616	0.148+j0.034	0.087+j0.040	14790.5	260	320
4/0 (19)	0.051	0.064	0.034	0.042	0.258	0.670	0.117+j0.030	0.071+j0.038	18652.0	295	360
250 (37)	0.0431	0.054	0.031	0.040	0.278	0.723	0.097+j0.026	0.062+j0.035	23110.1		

* Calculations are based on three cables triplexed / concentric shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on Figure 7 of ICEA T-117-734 (Single circuit trefoil, 100% load factor, 90°C conductor temperature, earth RHO 90, 36" burial depth)

‡ Ampacities are based on Figure 1 of ICEA T-117-734 (Single circuit trefoil, 100% load factor, 90°C conductor temperature, earth RHO 90, 36" burial depth)



Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension*
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	2 (1)	6.55	16.38	4.44	18.42	16x14	0.54	1.27	24.21	973	289.56	2363
TBA	2 (7)	7.19	17.02	4.44	19.05	16x14	0.54	1.27	24.84	1010	297.18	2363
TBA	1 (1)	7.34	17.17	4.44	19.20	13x12	0.42	1.27	25.81	1182	309.88	2982
TBA	1 (19)	8.18	18.01	4.44	20.04	13x12	0.42	1.27	26.64	1229	320.04	2982
TBA	1/0 (1)	8.25	18.08	4.44	20.12	16x12	0.34	1.27	26.72	1385	320.04	3760
TBA	1/0 (19)	9.19	19.02	4.44	21.06	16x12	0.34	1.27	27.66	1441	332.74	3760
TBA	2/0 (19)	10.29	20.12	4.44	22.15	13x10	0.26	1.27	29.87	1772	358.14	4739
TBA	3/0 (19)	11.58	21.41	4.44	23.44	16x10	0.21	1.27	31.17	2103	373.38	5972
TBA	4/0 (19)	13.00	22.83	4.44	24.87	16x9	0.17	1.27	33.22	2560	398.78	7534
TBA	250 (37)	14.17	24.23	4.44	26.26	25x10	0.14	1.27	33.99	2955	408.94	8900

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C†	Allowable Ampacity Directly Buried 90°C‡
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2 (1)	0.5315	0.67	0.0162	0.1608	0.535	1.3878	0.364+j0.071	0.206+j0.048	5856.3	155	195
2 (7)	0.5315	0.67	0.0152	0.1542	0.564	1.4665	0.364+j0.070	0.206+j0.047	5856.3	155	195
1 (1)	0.4232	0.53	0.0152	0.1575	0.571	1.4862	0.290+j0.057	0.164+j0.047	7560.0	175	220
1 (19)	0.4232	0.53	0.0140	0.1509	0.614	1.5945	0.290+j0.056	0.164+j0.046	7560.0	175	220
1/0 (1)	0.3346	0.42	0.0140	0.1509	0.617	1.6043	0.235+j0.047	0.132+j0.045	9304.6	200	250
1/0 (19)	0.3346	0.42	0.0131	0.1476	0.663	1.7224	0.235+j0.046	0.132+j0.044	9304.6	200	250
2/0 (19)	0.2657	0.33	0.0122	0.1444	0.715	1.8602	0.183+j0.039	0.106+j0.042	12017.3	225	285
3/0 (19)	0.2106	0.27	0.0113	0.1411	0.778	2.0210	0.148+j0.034	0.087+j0.040	14790.5	260	320
4/0 (19)	0.1673	0.21	0.0104	0.1378	0.846	2.1982	0.117+j0.030	0.071+j0.038	18652.0	295	360
250 (37)	0.1414	0.18	0.0094	0.1312	0.912	2.3720	0.097+j0.026	0.062+j0.035	23110.1		

* Calculations are based on three cables triplexed / concentric shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on Figure 7 of ICEA T-117-734 (Single circuit trefoil, 100% load factor, 90°C conductor temperature, earth RHO 90, 36" burial depth)

‡ Ampacities are based on Figure 1 of ICEA T-117-734 (Single circuit trefoil, 100% load factor, 90°C conductor temperature, earth RHO 90, 36" burial depth)

