



Southwire™

INSULATED METALLIC GROUNDING BUSHINGS WITH COPPER LAY-IN LUG - HOT DIP GALVANIZED

FEATURES

- Hot dip galvanized for superior protection against corrosion
- Copper lay-in lug
- Liner is rated flame retardant to 105°C
- UL listed for use with copper or aluminum grounding conductor

APPLICATIONS

- Use to provide a means of grounding Rigid or IMC conduit
- Indoor or outdoor use
- Use with locknut to terminate service conduit to a cabinet
- Lug provided for bonding jumper to a neutral bus bar
- Round surface of bushing prevents damage to wire insulation
- Plastic liner prevents damage to wire insulation

STANDARD MATERIAL

- Body - Malleable iron
- Plastic insulator
- Lug - Copper
- Clamping screw - Steel
- Set screws - Steel

STANDARD FINISH

- Body - Hot dip galvanized

CERTIFICATIONS

- UL Standard: UL 514B and UL 467
- RoHS
- Fed. Spec: A-A-50553
- NEMA: FB 1




331CMHDG



Conforms to finish thickness ASTM
A123/123M

PART #	SIZE	GROUNDING LUG WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
		MIN.	MAX.					
331CMHDG	1/2"	14	4	25	250	32	1.08"	.57"
332CMHDG	3/4"	14	4	25	250	35	1.31"	.57"
333CMHDG	1"	14	4	20	200	35	1.61"	.65"
334CMHDG	1-1/4"	14	4	15	150	30	1.91"	.71"
335CMHDG	1-1/2"	14	4	10	100	28	2.16"	.73"
336CMHDG	2"	14	4	10	100	29	2.72"	.73"
337CMHDG	2-1/2"	14	4	5	50	27	3.23"	.94"
338CMHDG	3"	14	4	---	25	14	3.88"	.94"
339CMHDG	3-1/2"	14	4	---	10	7	4.43"	.94"
340CMHDG	4"	14	4	---	10	8	4.89"	.94"



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.