



Southwire[®]
WE DELIVER POWER... RESPONSIBLY*

PRODUCT DATA SHEET

Controlled Document - Engineering Drive

1 Overlook Point, Suite 265
Lincolnshire, IL 60069
USA



SIGNA-WAVE™ - 400 SERIES Extra Flexible Communications Cable

Part Number	Designation	Jacket	1000' Stock Part Code
989400	Indoor/Outdoor Extra Flex	TPE	989400-06-08

Construction Specifications:

	Material	Diameter
Inner conductor	7/.0380" Bare Copper	0.108" Nom.
Dielectric	Foamed Polyethylene	0.295" Nom.
Outer Conductor	Bonded Aluminum Foil + Tinned Copper Braid	0.323" Nom.
Jacket	Thermoplastic Elastomer	0.405" Nom.

Electrical Properties:

Capacitance	23.9 pF/ft
Impedance	50 Ohms
Velocity	85%
Inner Conductor DC Resistance	1.07 (Ω/1000ft)
Outer Conductor DC Resistance	1.65 (Ω/1000ft)
Shielding Effectiveness	90 dB
Jacket Spark	8,000 VAC
Cutoff Frequency	16.2 GHz
Peak Power	16.0 kW
Voltage Withstand	2,500 VDC

Mechanical & Environmental Properties:

Minimum Bend Radius	1.00"
Storage Temperature	-94°F to 185°F
Installation Temperature	-40°F to 185°F
Operating Temperature	-40°F to 185°F

Attenuation & Average Power (68°F):

Frequency (MHz)	Typical Attenuation (dB/100ft)	Average Power (kW)
30	0.80	2.77
50	1.10	2.14
150	1.80	1.22
220	2.20	1.00
450	3.30	0.69
900	4.70	0.48
1500	6.20	0.36
1800	6.80	0.33
2000	7.20	0.31
2500	8.10	0.28
5800	13.00	0.17



This product complies with European Directive 2011/65/EU (RoHS-2)

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control, all product data presented is for informational purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of product(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire Company disclaims all liability in connection with the use of information contained herein or otherwise.

On special orders, the customer must accept all factory lengths and +/- 10% of the order quantity

Customer Approval:

Company Name: _____

Authorized Representative: _____ Date: _____

Specification Issue Date: March 4, 2009