



# Southwire™

## MASONRY BOX

### NON-GANGABLE, 2-1/2" & 3-1/2" DEEP - WTH CONDUIT KNOCKOUTS

#### FEATURES

- Concentric combination Knockouts

#### APPLICATIONS

- Masonry boxes are used as a junction box or to secure a wiring device in masonry block construction
- 2-1/2" deep boxes are used in 4" block walls, 3-1/2" deep boxes are used in 6" or 8" block walls

#### STANDARD MATERIAL

- Galvanized steel

#### CERTIFICATIONS

- UL Listed



LISTED



TB-125

PART #	DESCRIPTION	BOX DEPTH	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
			SIDE CONDUIT	BOTTOM CONDUIT		
TB-125	1 GANG	2-1/2"	(6) 1/2" – 3/4"	(2) 1/2" – 3/4"	13.8 (226.2)	20
TB-225	2 GANG		(8) 1/2" – 3/4"	(4) 1/2" – 3/4"	30.0 (491.7)	10
TB-325	3 GANG		(10) 1/2" – 3/4"	(6) 1/2" – 3/4"	45.0 (737.5)	10
TB-425	4 GANG		(12) 1/2" – 3/4"	(8) 1/2" – 3/4"	59.0 (966.9)	5
TB-525	5 GANG		(14) 1/2" – 3/4"	(10) 1/2" – 3/4"	74.0 (1212.7)	5
TB-625	6 GANG		(16) 1/2" – 3/4"	(12) 1/2" – 3/4"	92.0 (1507.7)	1
TB-135	1 GANG	3-1/2"	(8) 1/2" – 3/4"	(2) 1/2" – 3/4"	21.0 (344.2)	20
TB-235	2 GANG		(12) 1/2" – 3/4"	(4) 1/2" – 3/4"	44.0 (721.1)	10
TB-335	3 GANG		(16) 1/2" – 3/4"	(6) 1/2" – 3/4"	65.0 (1065.2)	10
TB-435	4 GANG		(20) 1/2" – 3/4"	(8) 1/2" – 3/4"	87.0 (1425.7)	5
TB-535	5 GANG		(24) 1/2" – 3/4"	(10) 1/2" – 3/4"	108.0 (1769.8)	1
TB-635	6 GANG		(28) 1/2" – 3/4"	(12) 1/2" – 3/4"	130.0 (2130.4)	1

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.



# Southwire™

## MASONRY BOX

NON-GANGABLE, 2-1/2" & 3-1/2" DEEP - WTH CONDUIT KNOCKOUTS



TB-225



TB-325



TB-425



TB-525



TB-625



TB-135



TB-235



TB-335



TB-435



TB-535



TB-635

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.