


## RIGID LB BODIES

Southwire® SIMPush™ Rigid conduit bodies are used as junction or pull boxes and are usually installed in an threaded or non-threaded, RMC, IMC, GRC, ARC and rigid stainless-steel conduit system to facilitate a change in direction.

### FEATURES:

- Corrosion-resistant copper-free diecast aluminum construction
- Raintight to prevent water from getting into conduit, box, or enclosure
- IP66 – Dust tight and protects against powerful jetting water
- Concrete-tight
- Provides continuous ground
- Powder-coated externally for corrosion resistance
- Internally coated with lubricating grease
- Tested to 100 removal cycles for reuse
- Locking teeth are constructed from zinc-plated steel
- Works with threaded or unthreaded conduit



**TO REMOVE THE SIMPush™ FITTING, SIMPLY SLIDE THE REMOVAL TOOL ONTO THE COLLAR AND PULL**


## 1/2" – 2"



**CERTIFICATIONS/RATINGS:**  
**NEMA FB RATED (4X)**  
**E-FILE #: E474806**



RMCLB050, RMCLB075, RMCLB100,  
RMCLB125, RMCLB150, RMCLB200



Stock #	Model #	Trade Size	Quantity Per Box	H (in.) A	W (in.) B	L (in.) C	Associated Removal Tool Model #	Removal Tool Included
<b>CONTRACTOR PACK</b>								
65080802	R-LB-050W	1/2"	4	5.336	1.31	3.06	R-RT-P1	-
65080902	R-LB-075W	3/4"	4	6	1.53	3.34	R-RT-P1	-
65081002	R-LB-100W	1"	4	6.81	1.74	3.83	R-RT-P2	-
65081102	R-LB-125W	1-1/4"	4	8.89	2.49	5.03	R-RT-P2	-
65081302	R-LB-150W	1-1/2"	4	8.84	2.49	5.06	R-RT-P3	-
65081402	R-LB-200W	2"	1	11.05	3.1	5.76	R-RT-P3	-

Project Name:

Contractor:

Address:

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | [SOUTHWIRETOOLS.COM](http://SOUTHWIRETOOLS.COM)

©2020 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.