

# Report of Test

## LLIA002372-014


Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)



### Performance Summary

Total Light Output	36357	lm	Illuminance at 10m	163.5 lux
Luminaire Power	232.8	W	Beam Distance	255.7 Meters (to 0.25 lux)
Luminous Efficacy	156.2	lm/W	Maximum Intensity	16348.5 cd
Beam Spread (50%)	86.7° V x 108.4° H			
Field Spread (10%)	125.1° V x 149.5° H			
NEMA Type	7H x 6V			

**PREPARED FOR : Topaz Lighting, A Southwire Company, 925 Waverly Ave, Holtsville, NY**



**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)

**Floodlight Summary:**

Report data based on absolute values as measured.

Maximum Luminous Intensity 16348.5 cd  
(Luminaire orientation as tested.) 1.7° vertical  
-1.0° horizontal

Beam Spread At 10% of max intensity 125.1° V x 149.5° H  
At 50% of max intensity 86.7° V x 108.4° H  
At 90% of max intensity 49.2° V x 54.7° H


Beam Flux Total 36357 lm  
To 10% of max intensity 35130 lm  
To 50% of max intensity 28096 lm  
To 90% of max intensity 10106 lm

Total Light Output 36356.8 lm

Signed:


\_\_\_\_\_  
Authorized Signatory

Date of test 8-Jul-2024  
Date of report 8-Jul-2024




**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)



Note: Left and right sides of photometric data have been averaged.  
Lumen values are tabulated as absolute lumen values.  
Candela values are tabulated as absolute candela values.



**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)


Vertical Angle (degrees)	Left Side Horizontal Angle (degrees)									Lumen Totals
	-90	-60	-30	0	30	60	90	126	180	
-90	12.6 0.0	31.0 0.2	39.0 0.5	47.9 0.9	59.6 1.4	62.8 1.7	72.6 2.1	77.4 2.5	80.7 2.7	12
	35.9 0.1	96.7 0.8	205.4 2.7	282.4 4.9	334.7 7.3	409.8 10.4	493.4 13.9	579.0 17.3	646.8 19.8	77
	58.6 0.2	268.4 2.3	520.6 6.7	668.5 11.9	841.1 18.3	1029.6 25.9	1235.1 34.2	1423.2 41.9	1559.0 47.1	189
-60	84.6 0.3	533.7 4.3	931.9 12.4	1379.3 24.3	1782.3 38.5	2143.9 54.0	2503.9 69.8	2786.4 82.9	2962.1 90.7	377
	127.6 0.6	797.8 6.5	1621.7 21.3	2504.0 45.0	3591.1 78.6	4726.4 118.8	5651.0 157.0	6272.4 185.8	6593.7 201.2	815
	165.7 0.8	1066.1 8.9	2420.1 31.5	4201.0 74.0	6374.0 137.9	8577.8 213.1	10087.6 276.8	10994.9 321.4	11420.9 344.1	1409
-30	196.0 1.0	1326.2 11.4	3211.8 42.4	5848.8 103.1	8939.5 192.3	11442.7 283.7	12908.9 354.8	13799.2 404.3	14221.5 429.6	1822
	217.4 1.1	1524.4 13.3	3853.1 51.3	7091.4 125.3	10571.4 227.0	12926.9 321.5	14342.4 394.8	15228.8 446.8	15657.4 473.6	2055
	228.7 1.2	1640.6 14.4	4232.8 56.3	7763.8 136.6	11273.4 241.7	13529.7 336.4	14910.0 410.2	15792.7 463.2	16226.9 490.6	2151
0	228.5 1.2	1654.8 14.5	4288.4 57.0	7839.4 137.9	11338.8 243.1	13584.4 337.8	14958.2 411.6	15838.9 464.6	16274.7 492.1	2160
	216.7 1.1	1563.0 13.6	4004.7 53.3	7330.0 129.3	10832.1 232.6	13162.2 327.4	14559.6 400.9	15444.8 453.3	15879.0 480.5	2092
	194.4 1.0	1378.6 11.9	3429.9 45.3	6251.2 110.1	9490.7 204.1	12043.6 298.7	13516.8 371.7	14415.5 422.6	14860.4 449.1	1914
30	162.8 0.8	1117.2 9.4	2646.9 34.6	4674.5 82.4	7147.5 154.5	9608.8 238.3	11245.3 308.0	12201.0 356.4	12665.4 381.3	1566
	122.9 0.6	835.0 6.8	1774.7 23.3	2850.4 51.2	4185.5 91.4	5595.9 140.2	6740.1 186.4	7494.5 221.0	7890.0 239.5	960
	77.8 0.3	547.1 4.5	963.4 13.0	1470.8 25.8	1907.8 41.2	2260.0 57.2	2603.6 73.0	2867.2 85.9	3026.3 93.4	394
60	52.7 0.2	252.9 2.2	492.6 6.3	587.7 10.6	713.6 15.6	823.7 20.8	923.5 25.8	1012.4 30.2	1074.2 32.9	145
	32.0 0.1	72.0 0.6	165.9 2.2	199.2 3.5	207.1 4.5	211.5 5.6	229.6 6.8	252.2 7.7	266.8 8.5	39
	11.1 0.0	21.8 0.2	19.7 0.2	18.0 0.3	21.5 0.5	10.0 0.3	5.9 0.1	1.0 0.0	0.4 0.0	2
90	11	126	460	1077	1931	2792	3498	4008	4277	18178

**Lumen Totals**

Legend:

candelas
lumens

Standard table of intensity and illuminance in accordance with IES procedures.  
Angular data is shown with the polar axis horizontal.  
Luminous flux expressed as lumens within marked zones.  
Luminous intensity expressed as candelas at centre of zones.



**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)


Vertical Angle (degrees)	Right Side Horizontal Angle (degrees)									Lumen Totals
	0	30	60	90	120	150	180	210	240	
-90	80.7 2.7	77.4 2.5	72.6 2.1	62.8 1.7	59.6 1.4	47.9 0.9	39.0 0.5	31.0 0.2	12.6 0.0	12
	646.8 19.8	579.0 17.3	493.4 13.9	409.8 10.4	334.7 7.3	282.4 4.9	205.4 2.7	96.7 0.8	35.9 0.1	77
	1559.0 47.1	1423.2 41.9	1235.1 34.2	1029.6 25.9	841.1 18.3	668.5 11.9	520.6 6.7	268.4 2.3	58.6 0.2	189
-60	2962.1 90.7	2786.4 82.9	2503.9 69.8	2143.9 54.0	1782.3 38.5	1379.3 24.3	931.9 12.4	533.7 4.3	84.6 0.3	377
	6593.7 201.2	6272.4 185.8	5651.0 157.0	4726.4 118.8	3591.1 78.6	2504.0 45.0	1621.7 21.3	797.8 6.5	127.6 0.6	815
	11420.9 344.1	10994.9 321.4	10087.6 276.8	8577.8 213.1	6374.0 137.9	4201.0 74.0	2420.1 31.5	1066.1 8.9	165.7 0.8	1409
-30	14221.5 429.6	13799.2 404.3	12908.9 354.8	11442.7 283.7	8939.5 192.3	5848.8 103.1	3211.8 42.4	1326.2 11.4	196.0 1.0	1822
	15657.4 473.6	15228.8 446.8	14342.4 394.8	12926.9 321.5	10571.4 227.0	7091.4 125.3	3853.1 51.3	1524.4 13.3	217.4 1.1	2055
	16226.9 490.6	15792.7 463.2	14910.0 410.2	13529.7 336.4	11273.4 241.7	7763.8 136.6	4232.8 56.3	1640.6 14.4	228.7 1.2	2151
0	16274.7 492.1	15838.9 464.6	14958.2 411.6	13584.4 337.8	11338.8 243.1	7839.4 137.9	4288.4 57.0	1654.8 14.5	228.5 1.2	2160
	15879.0 480.5	15444.8 453.3	14559.6 400.9	13162.2 327.4	10832.1 232.6	7330.0 129.3	4004.7 53.3	1563.0 13.6	216.7 1.1	2092
	14860.4 449.1	14415.5 422.6	13516.8 371.7	12043.6 298.7	9490.7 204.1	6251.2 110.1	3429.9 45.3	1378.6 11.9	194.4 1.0	1914
30	12665.4 381.3	12201.0 356.4	11245.3 308.0	9608.8 238.3	7147.5 154.5	4674.5 82.4	2646.9 34.6	1117.2 9.4	162.8 0.8	1566
	7890.0 239.5	7494.5 221.0	6740.1 186.4	5595.9 140.2	4185.5 91.4	2850.4 51.2	1774.7 23.3	835.0 6.8	122.9 0.6	960
	3026.3 93.4	2867.2 85.9	2603.6 73.0	2260.0 57.2	1907.8 41.2	1470.8 25.8	963.4 13.0	547.1 4.5	77.8 0.3	394
60	1074.2 32.9	1012.4 30.2	923.5 25.8	823.7 20.8	713.6 15.6	587.7 10.6	492.6 6.3	252.9 2.2	52.7 0.2	145
	266.8 8.5	252.2 7.7	229.6 6.8	211.5 5.6	207.1 4.5	199.2 3.5	165.9 2.2	72.0 0.6	32.0 0.1	39
	0.4 0.0	1.0 0.0	5.9 0.1	10.0 0.3	21.5 0.5	18.0 0.3	19.7 0.2	21.8 0.2	11.1 0.0	2
90	4277	4008	3498	2792	1931	1077	460	126	11	18178

**Lumen Totals**

Legend:

candelas
lumens

Standard table of intensity and illuminance in accordance with IES procedures.  
Angular data is shown with the polar axis horizontal.  
Luminous flux expressed as lumens within marked zones.  
Luminous intensity expressed as candelas at centre of zones.



**Test Report No. LLIA002372-014**


Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)

**Candela trace through origin.**

Vertical Trace			
Angle	Intensity (cd)	Angle	Intensity (cd)
90.0	0.00	0.0	16311.86
87.0	0.00	-3.0	16278.87
84.0	0.00	-6.0	16209.16
81.0	0.67	-9.0	16090.45
78.0	84.81	-12.0	15925.04
75.0	303.97	-15.0	15695.83
72.0	470.27	-18.0	15374.49
69.0	684.17	-21.0	14961.91
66.0	955.65	-24.0	14457.48
63.0	1300.69	-27.0	13852.95
60.0	1751.10	-30.0	13126.35
57.0	2375.21	-33.0	12228.52
54.0	3261.64	-36.0	11116.50
51.0	4524.76	-39.0	9774.51
48.0	6142.72	-42.0	8233.47
45.0	7901.36	-45.0	6556.23
42.0	9754.60	-48.0	5099.85
39.0	11287.68	-51.0	3974.16
36.0	12441.41	-54.0	3149.11
33.0	13323.90	-57.0	2528.79
30.0	14025.38	-60.0	2093.21
27.0	14593.76	-63.0	1771.91
24.0	15054.12	-66.0	1478.64
21.0	15425.16	-69.0	1201.67
18.0	15698.44	-72.0	926.80
15.0	15909.21	-75.0	653.59
12.0	16070.14	-78.0	409.43
9.0	16189.65	-81.0	222.03
6.0	16269.06	-84.0	92.56
3.0	16310.78	-87.0	24.54
0.0	16311.86	-90.0	5.76

Horizontal Trace			
Angle	Intensity (cd)	Angle	Intensity (cd)
90.0	1.10	0.0	16311.86
87.0	83.10	-3.0	16329.46
84.0	281.01	-6.0	16279.61
81.0	708.94	-9.0	16191.69
78.0	1136.87	-12.0	16049.89
75.0	1564.80	-15.0	15868.07
72.0	2363.96	-18.0	15650.88
69.0	3163.12	-21.0	15388.46
66.0	3962.29	-24.0	15090.92
63.0	4956.74	-27.0	14751.54
60.0	6048.84	-30.0	14370.90
57.0	7140.94	-33.0	13948.95
54.0	8243.24	-36.0	13440.76
51.0	9365.92	-39.0	12866.32
48.0	10488.60	-42.0	12225.62
45.0	11397.28	-45.0	11397.28
42.0	12225.62	-48.0	10488.60
39.0	12866.32	-51.0	9365.92
36.0	13440.76	-54.0	8243.24
33.0	13948.95	-57.0	7140.94
30.0	14370.90	-60.0	6048.84
27.0	14751.54	-63.0	4956.74
24.0	15090.92	-66.0	3962.29
21.0	15388.46	-69.0	3163.12
18.0	15650.88	-72.0	2363.96
15.0	15868.07	-75.0	1564.80
12.0	16049.89	-78.0	1136.87
9.0	16191.69	-81.0	708.94
6.0	16279.61	-84.0	281.01
3.0	16329.46	-87.0	83.10
0.0	16311.86	-90.0	1.10


Note: Luminaire orientation as tested.  
The left and right sides of photometric data have been averaged.



**Test Report No. LLIA002372-014**


Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)

**Candela trace through origin**



Note: The intensity units are expressed as candelas.  
The left and right sides of photometric data have been averaged.  
Both the vertical and the horizontal trace pass through the nadir.






**Test Report No. LLIA002372-014**


Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)

**Isolux Diagram**



Note: The isolux levels are based on a mounting height of H = 10.0 metres. Grid values show multiples of mounting height.  
The isolux contours are set to 10%, 20%, 30%, 50%, 70%, 90% of the maximum.  
The isolux contour units are expressed as lux. The left and right sides of photometric data have been averaged.






**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)





**Test Report No. LLIA002372-014**

Catalog Number: FL-290PCS-SFYK - 240W Setting - 4000K Setting  
Knuckle or trunion mounted, formed aluminum housing, white plastic reflector, clear glass enclosure, plastic optics over top of LEDs  
960 LEDs, 480 cool white and 480 warm white LEDs  
One LiFud LF-FAC320 LED driver  
119.9Vac, 60.00Hz, 1.947A, 232.8W, 0.997PF, 4.8%THD(i)

**Test Distance** 9.5 m  
**Test Temperature** 25.5 °C

**Notes** The laboratory has not participated in the selection of samples to be tested. All testing is performed on the understanding that the significance of the report is limited to the extent that the test sample is representative of production units.

Tested in accordance with the applicable sections of publications: IES LM-79-19, IES LM-75-19, and IES LM-35-20.

The luminous intensity values, and other derived quantities, contained in this report are based on the absolute data, as measured.

Prorating the performance of the sample for the use of other component combinations (such as lamp / LED / Ballast / driver), or for use in different environmental conditions than that tested, may produce erroneous results.

This report is free of erasures and corrections.

Photometric intensity values are reported using the CIE (B,  $\beta$ ) coordinate system as defined in CIE publication number 121.

This report may contain data that are not covered by the NVLAP accreditation. Quantities marked with \* are not covered.

This report must not be used by the customer to claim product certification, approval or endorsement by NVLAP, NIST, or any agency of the Federal Government.