



# Southwire™

## LED STRING LIGHT - X UPLIGHT

- Each LED head delivers 2200 lumens:
  - 2000 Lumens Downward
  - 200 Lumens Upward
- 4-Way Mounting Loop
- Available in 50' & 100' Lengths
- NEMA 5-15 and L5-20 Options Available
- Daisy Chain Receptacle Included
- Rugged IP65 Rated Plastic Housings
- Heavy Duty 16/3 Cord
- Diffused Anti Glare Lens



**2200 LUMENS  
PER HEAD**

**120VAC  
50/60HZ**

**100FT = 160W  
50FT = 80W**

**DIFFUSED ANTI  
GLARE LENS**

**ANTI-TWISTING  
HANGING PORTS:  
• 4 WAY "X" HANGING LOOP  
• VERTICAL HANGING LOOPS**



| MODEL #   | UPC          | DESCRIPTION   | HEIGHT | WIDTH | LENGTH | WEIGHT  |
|-----------|--------------|---|--------|-------|--------|---------|
| 71X5SW    | 032886297113 | 100ft LED String Light - X Uplight                  | 17"    | 9"    | 12"    | 16 lbs. |
| 71X4SW    | 032886297120 | 50ft LED String Light - X Uplight                   | 12"    | 9"    | 9"     | 8 lbs.  |
| 71X5SW520 | 032886297137 | 100ft LED String Light - X Uplight L5-20 Twist Lock | 17"    | 9"    | 12"    | 16 lbs. |
| 71X4SW520 | 032886297144 | 50ft LED String Light - X Uplight L5-20 Twist Lock  | 12"    | 9"    | 9"     | 8 lbs.  |

| MODEL #   | CARTON QTY | CORD GAUGE | WEATHER RATING | POWER OUTLET | MAX CHAIN LENGTH | LENS MATERIAL | CERTIFICATION   | WORKING TEMP   | CRI | REPLACEMENT PARTS |
|-----------|------------|------------|----------------|--------------|------------------|---------------|-----------------|----------------|-----|-------------------|
| 71X5SW    | 2          | 16/3 SJTW  | Wet Location   | NEMA 5-15R   | 500 ft           | Polycarbonate | cETL, FCC, ICES | -25°F to 130°F | 80  | Light Head: X5111 |
| 71X4SW    | 4          | 16/3 SJTW  | Wet Location   | NEMA 5-15R   | 500 ft           | Polycarbonate | cETL, FCC, ICES | -25°F to 130°F | 80  | Light Head: X5111 |
| 71X5SW520 | 2          | 16/3 SJTW  | Wet Location   | NEMA L5-20R  | 500 ft           | Polycarbonate | cETL, FCC, ICES | -25°F to 130°F | 80  | Light Head: X5111 |
| 71X4SW520 | 4          | 16/3 SJTW  | Wet Location   | NEMA L5-20R  | 500 ft           | Polycarbonate | cETL, FCC, ICES | -25°F to 130°F | 80  | Light Head: X5111 |

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2022 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.