



# Southwire™

## VAPORPROOF FIXTURES

### FEATURES

- Ceiling, wall or pendant mounting
- All assembled fixtures are equipped with 5 holes and available with 1/2" & 3/4" threaded holes
- Socket with leads
- Heat resistant glass globe
- Prevents moisture entry
- Industrial grade, fully gasketed
- Designed to protect the interior from deteriorating effect of ice, corrosive fumes, and non-explosive vapors
- Gray

### APPLICATIONS

- UL listed for wet locations
- Maintains illumination for safety and performance in inclement weather
- Input Voltage: 120V

### STANDARD MATERIAL

- Rugged die cast copper free aluminum

### STANDARD FINISH

- Premium powder coat finish



VF100W50- 1/2"  
VF100W75- 3/4"



VF1GLS



VF1CC



VFIBOX50-1/2"  
VFIBOX75-3/4"



VF100W50CG-1/2"  
VF100W75CG-3/4"



VF1100W50CG-1/2"  
VF1100W75CG-3/4"  
VF1200W50CG-1/2"  
VF1200W75CG-3/4"



VFW100W50CG-1/2"  
VFW100W75CG-3/4"

Rev. 0, 06/23


**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM


©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.




## VAPORPROOF FIXTURES




VF1100W50- 1/2"  
VF1100W75- 3/4"




VF1100W50CG-1/2"  
VF1100W75CG-3/4"  
VF1200W50CG-1/2"  
VF1200W75CG-3/4"




VFP100W50CG-1/2"  
VFP100W75CG-3/4"




VFW100W50CG-1/2"  
VFW100W75CG-3/4"



VFICC



VFGLS



VFIBOX50-1/2"  
VFIBOX75-3/4"

| PART #                           | # OF HOLES | THREAD SIZE | SHIP CASE | WEIGHT/ CASE (LBS.) | A     | B      | C     |
|----------------------------------|------------|-------------|-----------|---------------------|-------|--------|-------|
| VF1100W50*                       | 5          | 1/2"        | 6         | 13                  | 5.25" | 8.50"  | 3.25" |
| VF1100W75*                       | 5          | 3/4"        | 6         | 13                  | 5.25" | 8.50"  | 3.25" |
| VF1100W50CG*                     | 5          | 1/2"        | 6         | 16                  | 5.25" | 9"     | 4.13" |
| VF1100W75CG*                     | 5          | 3/4"        | 6         | 16                  | 5.25" | 9"     | 4.13" |
| VF1200W50CG**                    | 5          | 1/2"        | 6         | 16                  | 5.25" | 11.50" | 5.15" |
| VF1200W75CG**                    | 5          | 3/4"        | 6         | 16                  | 5.25" | 11.50" | 5.15" |
| VFIBOX50                         | 5          | 1/2"        | 12        | 13                  | 5.25" | 3.50"  | 4.13" |
| VFIBOX75                         | 5          | 3/4"        | 12        | 13                  | 5.25" | 3.50"  | 4.13" |
| VFP100W50CG*                     | -          | 1/2"        | 6         | 16                  | 4.13" | 10.25" | 3.88" |
| VFP100W75CG*                     | -          | 3/4"        | 6         | 16                  | 4.13" | 10.25" | 3.88" |
| VFW100W50CG*                     | 5          | 1/2"        | 6         | 19                  | 7.25" | 10"    | 4.13" |
| VFW100W75CG*                     | 5          | 3/4"        | 6         | 19                  | 7.25" | 10"    | 4.13" |
| <b>VAPORPROOF 7" GLASS GLOBE</b> |            |             |           |                     |       |        |       |
| VFGLS                            |            |             | 6         | 6                   | 3.25" | 7"     | 3"    |
| <b>7" CAST CAGE</b>              |            |             |           |                     |       |        |       |
| VFICC                            |            |             | 16        | 11                  | 4.25" | 7.25"  | 4.13" |

**UL Listing:**

Suitable for wet locations for use in dwellings. Suitable for use with 90° C supply wiring. Complies with UL Standard 1598. For non-hazardous locations where the lamp, socket and wiring require protection from rain, corrosive fumes, non-explosive vapors and gases.

\*Approved for maximum 100W incandescent. \*\*Approved for maximum 200W incandescent.

