



Southwire®
WE DELIVER POWER...RESPONSIBLY®

PRODUCT DATA SHEET

Controlled Document – Engineering Drive

1 Overlook Point, Suite 265
Lincolnshire, IL 60069
USA

PART NUMBER: 988596
DESCRIPTION: RG-174/U COAXIAL CABLE FULL SWEPT PER MIL-DTL-17
RATING: MIL-DTL-17 Qualified Products List (QPL)

Construction Parameters:

		<u>Wall (in)*</u>	<u>OD (in)*</u>
Conductors:	26 AWG (7/.0063) Copper Coated Steel (40% conductivity)		0.019
Dielectric:	Solid Polyethylene color natural	0.021	0.060
Shielding:	86% Tinned Coated Copper Braid		0.078
Jacket:	PVC (Non-Contaminating Vinyl)	0.016	0.110

Electrical Properties:

	<u>VALUE*</u>
Conductor Resistance (Max./100 ft)	9.67
Impedance (ohms):	50
Capacitance (Max. pF/ft):	32.2
Velocity of Propagation (%):	66
Attenuation (Max. db/100 ft): 50 MHz	6.5
100 MHz	10.0
400 MHz	25.0
1000 MHz	45.0
SRL (Min: dB): 100 MHz	23
500 MHz	20
800 MHz	19
1000 MHz	19

Cable Cross-section:

(NOT TO SCALE)



Miscellaneous Information:

Jacket Color: Black
Jacket Print (White): COLEMAN CABLE 988596 M17/119-RG174 MIL-DTL-17
OXDS2
Ink Jet Print (Blue): XXXXXX (Date Code)
"Coleman Cable LLC, is a wholly owned subsidiary of Southwire Company LLC"
Applicable MIL-DTL-17: M17/119G-RG174
Approximate Weight (lb/1000 ft): 9

This product complies with European Directive 2011/65/EU (RoHS-2)

On special orders the customer will accept all factory lengths and $\pm 10\%$ of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We reserve the right to review and modify all constructions to conform with the latest Regulatory requirement. We disclaim all liability in connection with the use of information contained herein or otherwise. This specification is propriety intellectual property of SOUTHWIRE. Any information contained herein shall not be disclosed to any party without written consent of SOUTHWIRE.