



Southwire™

RIGID CONDUIT BODIES

THREADED LL TYPE - HOT DIP GALVANIZED

FEATURES

- Hot dip galvanized finish provides superior protection against severe environmental factors

APPLICATION

- Compatible with all Form 5 & Form 35 series conduit bodies and covers
- Provides taps for branch conduit runs
- Enables 90° bends in conduit runs

STANDARD MATERIAL

- Malleable iron

STANDARD FINISH

- Hot dip galvanized

CERTIFICATIONS


- UL Standard: UL 514A and UL514D
- Fed. Spec: A-A-50563
- NEMA: FB 1



LL1MHDG



Conforms to finish thickness ASTM A123/123M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
LL1MHDG	1/2"	---	---	4.5	10	7	4.69"	1.46"	2.08"
LL2MHDG	3/4"	3	6 AWG	7.5	10	10	5.42"	1.65"	2.31"
LL3MHDG	1"	3	4 AWG	12.5	5	6	6.28"	1.98"	2.68"
LL4MHDG	1-1/4"	3	2 AWG	32.3	5	13	8.12"	2.60"	3.41"
LL5MHDG	1-1/2"	3	1/0 AWG	35.3	2	6	8.15"	2.80"	3.45"
LL6MHDG	2"	3	4/0 AWG	73	1	6	10.53"	3.52"	4.15"
LL7MHDG	2-1/2"	3	300 MCM	142	1	10	13.76"	3.98"	5.86"
LL8MHDG	3"	3	350 MCM	173	1	13	13.82"	4.65"	5.92"
LL9MHDG	1/2"	3	350 MCM	300	1	22	16.65"	5.43"	7.14"
LL10MHDG	4"	3	350 MCM	330	1	24	16.65"	5.74"	7.19"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.