




WELDING HAND TOOL DIMENSIONS


F = MAXIMUM OPENING

Description	Model #	A	B	C	D	E	F
Locking Clamps with Swivel Pads	LCS6	3.4"	3.4"	7.2"	2"	1.9"	2.8"
	LCS9	4.4"	4.7"	9.6"	2.8"	2.7"	4"
	LCS11	5.4"	5"	11.3"	34.6"	2.6"	4.2"
	LCS18	6"	11.6"	18.3"	3.9"	9.5"	11"


F = MAXIMUM OPENING

Description	Model #	A	B	C	D	E	F
Locking Clamps	LC6	3.3"	2.9"	6.5"	2.1"	1.6"	2"
	LC11	5.5"	4.8"	10.9"	3.7"	3.1"	4.1"
	LC18	6.1"	11.9"	18.3"	4"	10.3"	11"
	LCDR18	9.6"	11.5"	19"	7.7"	10"	6.1"


C = MAXIMUM OPENING

Description	Model #	A	B	C
Straight Jaw Locking Pliers	SLP7	7.2"	2.5"	1.6"
	SLP10	9.1"	2.8"	2.8"


C = MAXIMUM OPENING

Description	Model #	A	B	C
Curved Locking Pliers	CLP4W	4.4"	1.4"	1.2"
	CLP5W	5.4"	1.6"	1.2"
	CLP7W	7.3"	2.1"	1.8"
	CLP10W	9.1"	2.5"	2.4"



C = MAXIMUM OPENING

Description	Model #	A	B	C
Locking Welding Clamp	LWC9	9"	2.6"	2.5"




C = MAXIMUM OPENING

Description	Model #	A	B	C
Locking Sheet Metal Tool	LSM8	7.9"	2.7"	1.2"




C = MAXIMUM OPENING

Description	Model #	A	B	C
MIG Pliers	MIGP8	8.4"	2.1"	1.8"




C = MAXIMUM OPENING

Description	Model #	A	B	C
Ground Clamps	CGC200	7"	3.2"	1.4"
	SGC500	6.9"	3.4"	1.7"



C = MAXIMUM OPENING

Description	Model #	A	B	C	D
F Clamp	FC12	15.5"	7.8"	12.5"	6"



Description	Model #	A	B
Locking Chain Clamp	LCCH20	9"	2.5"