



Southwire™

4" SQUARE COVERS

UNIVERSAL INDUSTRIAL EXPOSED WORK COVERS, RAISED 1/2"

FEATURES

- Crushed corner design allow for use of standard box cover screws
- Flush adapter design creates smooth uniform look
- Device mounting hardware included

APPLICATION

- 4" square 1/2" raised universal industrial surface covers are used to attach devices directly onto 4" square boxes in a industrial/commercial setting

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- cULus
- UL Listed




G1943-U




G1950-U



G1947-U



G1943-U



G1950-U



G1947-U



PART #	DEVICES	CUBIC INCHES (CM3)	MASTER QTY
G1943-U	UNIVERSAL 1 DEVICE: 1.79", 1.59" OR 1.406 DIAMETER HOLE	7.0 (114.8)	10
G1950-U	UNIVERSAL 2 DEVICE: 2 GFCI, 2 TOGGLE, 2 DUPLEX	7.0 (114.8)	10
G1947-U	UNIVERSAL 1 DEVICE: GFCI, TOGGLE, DUPLEX	7.0 (114.8)	10

Rev. 0, 07/25

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

SNAP-IN CONNECTORS

DOUBLE SNAP LOCK - ZINC

APPROVED CABLES

PART #	SIZE	KO	CABLE TYPE	CONDUIT, SIZE/ CABLE, AWG	CABLE DIAMETER RANGE (IN)
38ASTSW	3/8	1/2	AC CABLE, ALUMINUM	14/2 – 10/3	0.405 – 0.612
			AC CABLE, STEEL	14/2 – 10/3	0.451 – 0.593
			METAL CLAD CABLE, MCI-A, STEEL	14/2 – 10/3	0.451 – 0.593
			METAL CLAD CABLE, MCI-A, ALUMINUM	14/2 – 10/3	0.439 – 0.58
			FMC, STEEL	3/8"	0.56 – 0.61
			FMC, ALUMINUM	3/8"	0.56 – 0.61
			RWFMC, STEEL	3/8"	0.56 – 0.61
			RWFMC, ALUMINUM	3/8"	0.56 – 0.61
			METAL CLAD CABLE, MCC, ALUMINUM	14/2 – 10/3	0.451 – 0.593
			HCF ARMORED CABLE, STEEL	12/2 – 10/3	0.470 – 0.610
			HCF ARMORED CABLE, ALUMINUM	14/2 – 10/3	0.402 – 0.610
40ASTSW	1/2	1/2	AC CABLE, ALUMINUM	14/3 – 10/3	0.485 – 0.612
			AC CABLE, STEEL	14/3 – 10/3	0.464 – 0.58
			METAL CLAD CABLE, MCI-A, STEEL	14/3 – 10/3	0.464 – 0.593
			METAL CLAD CABLE, MCI-A, ALUMINUM	14/3 – 10/3	0.464 – 0.593
			FMC, STEEL	3/8"	0.56 – 0.61
			FMC, ALUMINUM	3/8"	0.56 – 0.61
			RWFMC, STEEL	3/8"	0.56 – 0.61
			RWFMC, ALUMINUM	3/8"	0.56 – 0.61
			METAL CLAD CABLE, MCC, ALUMINUM	14/3 – 10/3	0.464 – 0.593
			HCF ARMORED CABLE, STEEL	12/2 – 10/3	0.470 – 0.610
			HCF ARMORED CABLE, ALUMINUM	14/2 – 10/3	0.402 – 0.610

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.