



Southwire™

COMPRESSION LUGS

TWO HOLE - SHORT BARREL

FEATURES

- Produced from high conductivity copper tubing and suitable for heavy duty applications
- Tin-plated to provide corrosion resistance
- Color coded

APPLICATIONS

- Listed for 35 KV maximum when properly installed
- Ideal for direct burial in earth or concrete and grounding applications

STANDARD MATERIAL


- Copper

STANDARD FINISH

- Tin plated



2921



PART #	WIRE SIZE	COLOR CODE	BOLT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C = HOLE SPACING
2921	#8	RED	10	100	1000	20	2.50"	.45"	.625"
2922	#6	BLUE	1/4"	100	1000	23	2.56"	.45"	.625"
2923	#4	GRAY	1/4"	100	1000	28	2.34"	.50"	.625"
2925	#2	BROWN	5/16"	50	500	26	2.58"	.61"	.75"
2925A	#2	BROWN	3/8"	50	500	26	3.05"	.61"	.75"
2926	1/0	PINK	5/16"	25	250	20	3.14"	.75"	.875"
2927	2/0	BLACK	3/8"	25	250	23	3.24"	.83"	1.75"
2927A	2/0	BLACK	1/2"	25	250	31	4.17"	.83"	1.75"
2928	3/0	ORANGE	1/2"	25	250	36	4.25"	.91"	1.75"
2929	4/0	PURPLE	1/2"	20	200	36	4.28"	1.02"	1.75"
2929A	250 MCM	YELLOW	1/2"	10	100	24	4.41"	1.11"	1.75"
2929B	300 MCM	WHITE	1/2"	10	100	26	4.53"	1.24"	1.75"
2930	350 MCM	RED	1/2"	5	50	17	4.53"	1.24"	1.75"
2931	400 MCM	BLUE	1/2"	5	50	20	4.81"	1.34"	1.75"
2932	500 MCM	BROWN	1/2"	5	50	27	4.88"	1.52"	1.75"
2933	600 MCM	GREEN	3/8"	5	50	35	4.49"	1.73"	1.75"
2934	750 MCM	BLACK	1/2"	5	50	44	4.79"	1.89"	1.75"

Rev. 0, 10/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.