



Southwire™

INSULATED METALLIC GROUNDING BUSHINGS WITH ALUMINUM LAY-IN LUG - ZINC DIE CAST

FEATURES

- Tin plated aluminum alloy 6061-T6 rated for AL and CU conductor
- Liner is rated flame retardant to 105°C
- UL listed for use with copper or aluminum grounding conductor

APPLICATIONS

- Use to provide a means of grounding Rigid or IMC conduit
- Indoor or outdoor use (lay-in lug)
- Use with locknut to terminate service conduit to a cabinet

- Lug provided for bonding jumper to a neutral bus bar
- Round surface of bushing prevents damage to wire insulation
- Plastic liner prevents damage to wire insulation

STANDARD MATERIAL


- Body - Zinc die cast
- Plastic insulator
- Lug - Aluminum
- Clamping screw - Steel
- Set screws - Steel



332



PART #	SIZE	GROUNDING LUG WIRE SIZE		INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B
		MIN.	MAX.					
331	1/2"	14	4	50	500	30	1.04"	.38"
332	3/4"	14	4	50	500	35	1.26"	.41"
333	1"	14	4	25	250	23	1.53"	.50"
334	1-1/4"	14	4	20	200	26	1.86"	.53"
334A	1-1/4"	14	1/0	20	200	26	1.86"	.53"
335	1-1/2"	14	4	10	100	16	2.13"	.56"
335A	1-1/2"	14	1/0	10	100	16	2.13"	.56"
336TZ	2"	14	4	10	100	21	2.60"	.66"
336A	2"	14	1/0	10	100	21	2.60"	.66"
337	2-1/2"	14	1/0	---	50	20	3.15"	.75"
337A	2-1/2"	6	250 MCM	---	50	20	3.15"	.75"
338	3"	14	1/0	---	50	29	3.76"	.75"
338A	3"	6	250 MCM	---	50	29	3.76"	.75"
339	3-1/2"	14	1/0	---	10	15	4.27"	.75"
339A	3-1/2"	6	250 MCM	---	10	15	4.27"	.75"
340	4"	14	1/0	---	10	20	4.76"	.75"
340A	4"	6	250 MCM	---	10	20	4.76"	.75"



Rev. 0, 05/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.