



Southwire™

RIGID CONDUIT BODIES

THREADED LR TYPE - MALLEABLE IRON

FEATURES

- NPT tapered hubs
- Suitable for use in concrete

APPLICATION

- Provides access to conductors for maintenance and future system changes

STANDARD MATERIAL

- Malleable iron

STANDARD FINISH


- Zinc plated, aluminum enameled

CERTIFICATIONS

- UL Standard: UL 514A
- Fed. Spec: W-C-586D
- NEMA: FB 1



LR1M



PART #	SIZE	WIRE SIZE		INTERNAL VOLUME (IN ³)	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B	C
		MAX. NUMBER	MAX. SIZE						
LR1M	1/2"	---	---	4.5	10	7	4.56"	1.31"	2.06"
LR2M	3/4"	3	6 AWG	7.5	10	9	5.31"	1.62"	2.23"
LR3M	1"	3	4 AWG	12.5	5	6	6.25"	1.88"	2.50"
LR4M	1-1/4"	3	2 AWG	32.3	5	23	8.22"	2.50"	3.40"
LR5M	1-1/2"	3	1/0 AWG	35.3	10	26	8.22"	2.67"	3.48"
LR6M	2"	3	4/0 AWG	73	5	26	10.48"	3.29"	4.07"
LR7M	2-1/2"	3	300 MCM	138	1	10	13.75"	4.45"	4.38"
LR8M	3"	3	350 MCM	170	1	13	13.75"	4.45"	4.38"
LR9M	1/2"	3	350 MCM	300	1	22	16.75"	5.80"	5.63"
LR10M	4"	3	350 MCM	328	1	24	16.75"	5.80"	5.63"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.