

## 3/C CU 2000V Type G-GC RHINOFLEX™ CPE Mining Cable 90°C

Flexible Copper conductors, Ethylene Propylene Rubber (EPR) insulation, Extra Heavy Duty Two Layer Chlorinated Polyethylene (CPE) Jacket with Optional Reflective Stripes



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Tin coated, soft drawn, annealed, flexible, rope-lay stranded copper per ASTM B33/B172
- Separator Tape:** Non-conducting tape applied between the conductor and insulation to facilitate stripping
- Insulation:** Ethylene Propylene Rubber (EPR), color coded black, white, red
- Ground Conductors:** Two mylar taped, tin coated, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B33/B172
- Ground Check Conductor:** Tin coated, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B33/B172 with yellow, high durometer, Ethylene Propylene Rubber (EPR) insulation
- Inner Jacket:** Black, mold cured, extra heavy-duty integral fill flame resistant, thermosetting Chlorinated Polyethylene (CPE)
- Reinforcement:** Reinforcing twine applied between the two jacket layers
- Outer Jacket:** Black, mold cured, extra heavy-duty, modified integral fill, flame resistant, thermosetting Chlorinated Polyethylene (CPE). Alternate jacket colors available
- Reflective Stripe:** Highly visible reflective stripe embedded into the outer jacket to increase safety and help prevent cable runover (optional, contact your sales representative for part number)

### APPLICATIONS AND FEATURES:

RHINOFLEX™ Type G-G cable is a heavy-duty cable for use where flexibility and maximum protection is required. For use with all portable, temporary, and permanent power applications such as mobile or stationary mining equipment, shuttle cars, mobile drills, pumps, roof bolters, conveyors, and any portable power where equipment grounding is required, it is ideal for use anytime extra-durable, flexible cable is required. Also suitable for continuous submersion in water. Ground check conductor provides fail-safe ground monitoring. Embossed print legend for easy cable identification. Cold Bend and Impact Tested to -50°C.

### SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- MSHA Approved



Southwire



Services

## SAMPLE PRINT LEGEND:

SOUTHWIRE (R) RHINO™ BRAND CABLE # AWG 3/C TYPE G-GC PORTABLE POWER CABLE 90°C WET OR DRY 2000V FT5 -50°C P-07-KA140024 MSHA

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Diameter Over Insulation	Ground Size	Ground Strands	Ground Check Size	Ground Check Strands	Ground Check Insulation Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	No.	inch	mil	inch	AWG	No.	AWG	No.	mil	inch	lb/1000ft
59126699	8	3	168	0.155	60	0.311	10	104	10	104	30	0.97	630
58555799	6	3	133	0.21	60	0.366	10	104	10	104	30	1.05	780
58502899	4	3	259	0.256	60	0.412	8	168	10	104	30	1.19	1080
TBA	3	3	259	0.285	60	0.441	8	168	10	104	30	1.25	1230
58572599	2	3	308	0.32	60	0.476	7	49	8	168	45	1.34	1480
58926899	1	3	385	0.355	80	0.551	6	133	8	168	45	1.51	1870
TBA	1/0	3	273	0.385	80	0.581	5	133	8	168	45	1.65	2290
58572699	2/0	3	324	0.42	80	0.616	4	259	8	168	45	1.75	2730
TBA	3/0	3	418	0.506	80	0.702	3	259	8	168	45	1.89	3260
58719799	4/0	3	532	0.577	80	0.773	2	308	8	168	45	2.04	3940
59019999	250	3	608	0.61	95	0.836	1	385	8	168	45	2.39	5060
58753199	350	3	855	0.72	95	0.946	1/0	273	8	168	45	2.68	6660
TBA	300	3	735	0.737	95	0.963	1	385	8	168	45	2.56	5710
TBA	400	3	980	0.831	95	1.057	1/0	273	6	133	60	2.82	7300
TBA	450	3	1127	0.894	95	1.120	2/0	324	6	133	60	2.94	8130
TBA	500	3	1221	0.9	95	1.126	3/0	418	6	133	60	3.03	9030

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item



**Southwire**



Services

**Table 2 – Electrical and Engineering Data**

Stock Number	Cond. Size	Cond. Number	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance	Inductive Reactance	Working Tension	Min Bending Radius	Allowable Ampacity In Air 90°C†
	AWG/Kcmil	No.	Ω/1000ft	Ω/1000ft	MΩ*1000ft	MΩ/1000ft	lb	inch	Amp
59126699	8	3	0.676	0.845	0.038	0.038	113.000	5.8	59
58555799	6	3	0.421	0.526	0.030	0.034	179.000	6.3	79
58502899	4	3	0.267	0.334	0.026	0.033	285.000	7.1	104
TBA	3	3	0.212	0.265	0.024	0.032	360.000	7.5	120
58572599	2	3	0.168	0.210	0.021	0.031	454.000	8	138
58926899	1	3	0.133	0.166	0.024	0.032	572.000	9.1	161
TBA	1/0	3	0.111	0.139	0.022	0.031	722.000	9.9	186
58572699	2/0	3	0.085	0.106	0.021	0.031	910.000	10.5	215
TBA	3/0	3	0.067	0.084	0.018	0.029	1147.000	11.3	249
58719799	4/0	3	0.053	0.066	0.016	0.028	1446.000	12.2	287
59019999	250	3	0.045	0.056	0.017	0.029	1709.000	14.3	320
58753199	350	3	0.032	0.040	0.015	0.028	2393.000	16.1	394
TBA	300	3	0.037	0.046	0.014	0.028	2051.000	15.4	357
TBA	400	3	0.027	0.034	0.013	0.027	2734.000	16.9	430
TBA	450	3	0.025	0.031	0.012	0.027	3075.000	17.6	460
TBA	500	3	0.023	0.029	0.012	0.027	3418.000	18.2	487

† Ampacity based on ICEA S-75-381 Table H-1 and is for a single isolated cable in air operated with an open-circuited shield at an ambient temperature of 40°C and a conductor temperature of 90°C



**Southwire**



Services