

SUMNER*

SERIES 1900 MATERIAL LIFT

STANDARD FEATURES

- 8' or 10' height (2.4 - 3.05 m)
- 350 - 400 lbs capacity
- Transportable
- Straddle Base - Standard
- Foot Pedal Brake

TELESCOPING ALUMINUM MASTS



FRONT VIEW

TRANSPORT WHEELS FOR VAN OR PICKUP



BACK VIEW

PART #	DESCRIPTION							WEIGHT (lbs)	WEIGHT (kg)	
782050	Series 1908, 8' H, 350 lbs							180 lbs	76 kg	
782051	Series 1910, 10' H, 400 lbs							172 lbs	78 kg	
	HEIGHT STOWED	FORKS UP	FORKS DOWN	WIDTH MAX	WIDTH MIN	INSIDE MAX	LENGTH STOWED	LENGTH OPERATING	WEIGHT	LOAD CAPACITY
1908	5' 8-1/4" 1.73 m	10' 3.0 m	8' 2" 2.49 m	3' 6-3/4" 1.08 m	2' 4-1/2" .72 m	3' 3/4" .93 m	1' 4.5" .42 m	3' 10" 1.16 m	168 lbs 76 kg	400 lbs 180 kg
1910	6' 7.5" 2.02 m	11' 8-5/6" 3.6 m	9' 9.5" 2.98 m	3' 6-3/4" 1.08 m	2' 4-1/2" .72 m	3' 3/4" .93 m	1' 4.5" .42 m	3' 10" 1.16 m	172 lbs 78 kg	350 lbs 160 kg