


SERIES 2412 CONTRACTOR LIFT

A Super Compact, Versatile Lift At A Great Price!

Series 2400 Features:

- ✓ Super Compact 12 ft (3.7 m)
- ✓ 450 lbs (200 kg) lift capacity
- ✓ One piece construction –no loose pieces
- ✓ Easily portable for one person operation
- ✓ Fits most SUVs and vans
- ✓ 12' 11-3/4" heights when forks reversed



Reversible Forks

Two plunger pins permit quick release of forks. Forks may be removed for storage or reversed for added height.

Inside-Mast Cable Feed

Cable feeds inside mast, removed from the operator for safety – similar to the 2000 and 2100 Series lifts.



The Perfect Lift For ...

- HVAC Contractors
- Electrical Contractors
- Industrial Maintenance
- Steel Erectors
- Facility Management

Pulley Guards

Contains load cable... line cannot come off.

Handle

Use convenient handle for “hand truck” mobility and to position lift at point of use.

Winch

Coffee grinder style winch features auto-braking and detachable winch handles.

Roller Wheels

Handy wheels located to ease rolling into vehicles for transportation.

**8" (20 cm)
non-marring wheels**

Series 2400 Contractor Lift	2412	
Part #	784750	
Height Max (forks up)	12' 11-3/4"	4.0 m
Height Max (forks down)	12'	3.7 m
Lift Capacity	450 lbs	200 kg
Height Stowed	62-3/4"	159.4 cm
Length Stowed	23"	58.4 cm
Length Operating	48"	121.9 cm
Width Stowed	26-3/8"	67.1 cm
Width Max	26-3/8"	67.1 cm
Winch Cranks per ft/m	8/ft	24/m
Basic Weight	195 lbs	88.5 kg

Double Row Casters

- ✓ Four 3" (7.5 cm) casters permit easy handling of heavy loads
- ✓ Swivel independently
- ✓ Lockable to insure safety
- ✓ Allow for multi-directional positioning of lift

