



Southwire™

CABLE TRAY BOX ROLLERS

HB1A-6 SPLIT BOX ROLLER, CLAMP-ON

- Easy-to-install clamp-on design, fast installation, great for straight cable runs, and installs on any depth cable tray
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- 6-roller design keeps cables fully captured during the cable pull
- Cable space between rollers is 3.25" x 4"
- "T"-handle with large diameter swivel base allows for secure clamping
- Hinged design opens greater than 90° for easy unloading of cables



HB1A-6

HB1A-9 UNIVERSAL SPLIT BOX ROLLER

- A heavy-duty box roller that may be mounted multiple ways on cable tray
- Flexible mounting above or inside the cable tray using standard HB3AX48 crossbar
- May be side-clamped using the optional STC, Side Tray Clamp
- Mount with heavy-duty force rollers on the top/bottom or side to accommodate top, bottom, or side pulling loads
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- 6-roller design keeps cables fully captured during the cable pull and great for risers, waterfalls, and horizontal turns
- Hinged design opens greater than 90° for easy unloading of cables
- Cable space between rollers is 5" x 4.8"



HB1A-9

HB1A-9STC UNIVERSAL SPLIT BOX ROLLER WITH SIDE TRAY CLAMP

- HB1A-9 with Side Tray Clamp allows this heavy-duty box roller to be mounted on any depth cable tray
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- 6-roller design keeps cables fully captured during the cable pull
- Mount with heavy-duty force rollers on the top/bottom or side to accommodate top, bottom, or side loads
- Cable space between rollers is 5" x 4.8"
- "T"-handle with large diameter swivel base allows for secure clamping



HB1A-9STC

HB1A-9X48 UNIVERSAL SPLIT BOX ROLLER WITH 48" CROSSBAR & CLAMPS

- Includes HB1A-9 Universal Split Box Roller, 48" Crossbar, and (2) HBFB Tray Clamps
- This configuration is suitable anywhere on the cable tray: horizontal turns, inside or outside risers, and straight sections
- Flexible mounting above or inside the cable tray
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- Cable space between rollers is 5" x 4.8"



HB1A-9X48

MODEL NUMBER	STOCK	DESCRIPTION	WORKING LOAD	HEIGHT	WIDTH	LENGTH	WEIGHT
HB1A-6	65094901	Split Box Roller, Clamp-On	300 lbs (136.0 kgs)	11.5 in (29.2 cm)	5.0 in (12.7 cm)	12.0 in (30.5 cm)	9.8 lbs (4.4 kg)
HB1A-9	65095101	Universal Split Box Roller	300 lbs (136.0 kgs)	11.5 in (29.2 cm)	6.9 in (17.4 cm)	12.6 in (31.9 cm)	14.1 lbs (6.4 kg)
HB1A-9STC	65103301	Universal Split Box Roller with Side Tray Clamp	300 lbs (136.0 kgs)	11.4 in (28.9 cm)	6.8 in (17.3 cm)	18.8 in (47.8 cm)	22.0 lbs (9.9 kg)
HB1A-9X48	65103501	Universal Split Box Roller with 48" Crossbar & Clamps	300 lbs (136.0 kgs)	16.0 in (40.6 cm)	6.8 in (17.3 cm)	48.0 in (121.9 cm)	27.1 lbs (12.2 kg)

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

CABLE TRAY BOX ROLLERS

HB9A OPEN-TOP BOX ROLLER

- A lightweight open-top box roller that saves time by allowing faster rope insertion and cable removal
- Great for straight runs and outside vertical risers
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- Flexible mounting above or inside the cable tray using standard HB3AX48 crossbar.
- Also compatible with the STC, Side Tray Clamp
- Cable space between rollers is 4.8"



HB9A

HB9AX48 OPEN-TOP BOX ROLLER WITH 48" CROSSBAR & CLAMPS

- Includes HB9A Open Top Box Roller, 48" Crossbar, and (2) HBFB Tray Clamps
- Flexible mounting above or inside the cable tray
- Great for guiding cable over outside vertical risers
- Premium construction: High-strength, one-piece die cast aluminum frame; only from Southwire!
- Cable space between rollers is 4.8"



HB9AX48

HB3AX48 48" CROSSBAR WITH CLAMPS

- Includes 48" crossbar with (2) HBFB tray clamps
- Compatible with HB1A-9 and HB9A
- Flexible mounting options allows HB1A-9 & HB9A to be located above or inside the tray
- For use with 4" - 6" deep cable tray



HB3AX48



MODEL NUMBER	STOCK	DESCRIPTION	WORKING LOAD	HEIGHT	WIDTH	LENGTH	WEIGHT
HB9A	65184040	Open-Top Box Roller	400 lbs (181.0 kgs)	11.5 in (29.2 cm)	6.6 in (16.8 cm)	8.9 in (22.6 cm)	13.2 lbs (5.9 kg)
HB9AX48	65104001	Open-Top Box Roller with 48" Crossbar & Clamps	400 lbs (181.0 kgs)	13.9 in (35.4 cm)	6.9 in (17.4 cm)	48.0 in (121.9 cm)	22.1 lbs (10.0 kg)
HB3AX48	65095401	48" Crossbar with Clamps	---	6.5 in (16.5 cm)	4.5 in (11.4 cm)	48.0 in (121.9 cm)	14.3 lbs (6.5 kg)

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

CABLE TRAY BOX ROLLERS

HBFB-EXT EXTENDED LENGTH TRAY CLAMP

- Enables mounting of HB1A-9 below cross bar and up to 12" above cable tray; pull one pin to unload cables into tray
- Use in place of HBFB to attach crossbar to cable tray
- Turn the "T"-handle to adjust the clamping height
- For use with 4" - 6" deep cable tray

STC SIDE TRAY CLAMP

- Allows HB1A-9 Universal Split Box Roller and HB9A Open-Top Box Roller to be clamped to the side of the tray
- Mounts on any depth cable tray
- Allows box rollers to be mounted horizontally or vertically to accommodate top, bottom, or side pulling loads
- "T"-handle with large diameter swivel base allows for secure clamping

HBFB TRAY CLAMP

- Use to attach crossbar to cable tray with 4" - 6" side rail height
- Threaded "T"-handle adjusts clamping depth from 4" - 6"

HB-90 90° BRACKET

- Use the 90° bracket with the HB1A-9 to improve mounting stability; this setup anchors the HB1A-9 on two sides
- Allows the larger HB1A-9 rollers to be positioned on the sides to accommodate side pulling loads



HBFB-EXT




STC



HBFB



HB-90



MODEL NUMBER	STOCK	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
HBFB-EXT	65095301	Extended Length Tray Clamp	17.8 in (45.2 cm)	6.0 in (15.2 cm)	3.8 in (9.7 cm)	7 lbs (3.2 kg)
STC	65183740	Side Tray Clamp	13.4 in (34.0 cm)	6.85 in (17.4 cm)	16.4 in (41.6 cm)	6.8 lbs (3.1 kg)
HBFB	65095501	Tray Clamp	6.5 in (16.5 cm)	2.0 in (5.1 cm)	4.5 in (11.4 cm)	3.4 lbs (1.5 kg)
HB-90	65095601	90° Bracket	9.8 in (24.9 cm)	1.7 in (4.3 cm)	3.6 in (9.1 cm)	3 lbs (1.4 kg)

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
 *Registered Trademark & ™Trademark of Southwire Company, LLC.